Cooling Fans

Centrifugal Blowers

Axial Flow

Overview, Product Series

Fans

AC Input Low-Power Consumption EMU

AC Input Compact Size

AC Input Large Size, Large Air Flow MRS

AC Input Long-Life MRE

DC Input MDS MD

DC Input Alarm MDA

DC Input Variable Flow MDV

DC Input Long-Life MDE

DC Input Splash Proof MDP

Cross Flow Fans

AC Input MF DC Input MFD

Enclosure Fan Modules

Thermostat

Accessories

Installation

AC Input MB Series DC Input MBD Series

Centrifugal Blowers

For details on this product please refer to our website.

www.orientalmotor.com/catalog



Centrifugal blowers provide directional air flow by maximizing static pressure, making them optimal for spot cooling and for air flow through a duct. Alternatively, their high suction can be used to hold an object in position or their directed air flow can be used to move objects.

Features

Since the exhaust outlet is reduced to focus air to a specified direction, these blowers are used for spot cooling. The static pressure is also high, which makes them a suitable choice when cooling equipment through which air cannot flow easily or when blowing air using a duct.


Types of Centrifugal Blowers

●: Standard Type ■: Alarm Tyl						m rype		
		Power Supply Voltage	Impeller Diameter [mm (in.)]					
Series	Features		ф160 (ф6.30)	ф120 (ф4.72)	ф100 (ф3.94)	ф80 (ф3.15)	ф60 (ф2.36)	ф50 (ф1.97)
AC Centrifugal Blower MB Series	■AC input centrifugal blowers ■The MB Series is recognized by UL/CSA Standards and conforms to EN Standards. CE Marking is used in accordance with the Low Voltage Directive. (Certification status differs according to the product.)	Three-Phase 220/230 VAC	*	•		•		
		Single-Phase 110/115 VAC	•	•	•	•	•	•
		Single-Phase 220/230 VAC	•	•	•	•	•	•
DC Centrifugal Blower	DC input centrifugal blowers	24 VDC		•	•	•		
MBD Series		48 VDC			•	•		

 \bigstar A three-phase 220 VAC version is not available.

Details of regulations and standards
 Page I-2
 For detailed information about regulations and standards, please see the Oriental Motor website.

System Configuration



Product Number

MB, MBD Series

Series MB: AC Centrifugal Blowers MB Series 1 MBD: DC Centrifugal Blowers MBD Series **5**: φ50 mm (φ1.97 in.), **6**: φ60 mm (φ2.36 in.), **8**: φ80 mm (φ3.15 in.) Impeller Diameter 2 **10**: ϕ 100 mm (ϕ 3.94 in.), **12**: ϕ 120 mm (ϕ 4.72 in.), **16**: ϕ 160 mm (ϕ 6.30 in.) Impeller Thickness 20: 20 mm (0.79 in.), 30: 30 mm (1.18 in.), 40: 40 mm (1.57 in.) 3 **55**: 55 mm (2.17 in.), **65**: 65 mm (2.56 in.) Power Supply T: Three-phase 220/230 VAC B: Single-phase 110/115 VAC Voltage 4 D: Single-phase 220/230 VAC 24: 24 VDC, 24A: 24 VDC Low-Speed Alarm, Contact Alarm Type 48: 48 VDC

Fan Kit

T- MB1255-D - GA

2

 Fan Kit Order Code Fan Product Name 2

A: With mounting bracket and installation screws

GA: With finger guard, mounting bracket and installation screws FA: With filter, mounting bracket and installation screws

Product line

MB Series

Impeller Diameter	Power Supply Voltage VAC	Fan Only		Fan Kit	
		Product Name	List Price	Product Name	List Price
ф50 mm (ф1.97 in.)	Single-Phase 110/115	MB520-B	\$45.00	T-MB520-B-A	\$50.00
	Single-Phase 220/230	MB520-D	\$47.00	T-MB520-D-A	\$52.00
ф60 mm (ф2.36 in.)	Single-Phase 110/115	MB630-B	\$47.00	T-MB630-B-A	\$52.00
	Single-Phase 220/230	MB630-D	\$49.00	T-MB630-D-A	\$54.00
ф80 mm (ф3.15 in.)	Three-Phase 220/230	мв840-т	#7C 00	T-MB840-T-GA	\$90.00
			\$76.00	T-MB840-T-FA	\$98.00
	Single-Phase 110/115	MB840-B	#70.00	T-MB840-B-GA	\$87.00
			\$73.00	T-MB840-B-FA	\$95.00
	Single-Phase 220/230	MB840-D	#7C 00	T-MB840-D-GA	\$90.00
			\$76.00	T-MB840-D-FA	\$98.00
ф100 mm (ф3.94 in.)	Single-Phase 110/115	MB1040-B	#00.00	T-MB1040-B-GA	\$102.00
			\$88.00	T-MB1040-B-FA	\$111.00
	Single-Phase 220/230	MB1040-D	#01.00	T-MB1040-D-GA	\$105.00
			\$91.00	T-MB1040-D-FA	\$114.00
ф120 mm (ф4.72 in.)	Three-Phase 220/230	MB1255-T	# 100.00	T-MB1255-T-GA	\$187.00
			\$168.00	T-MB1255-T-FA	\$197.00
	Single-Phase 110/115	MB1255-B	\$160.00	T-MB1255-B-GA	\$179.00
			\$160.00	T-MB1255-B-FA	\$189.00
	Single-Phase 220/230	MB1255-D	#1C0.00	T-MB1255-D-GA	\$187.00
			\$168.00	T-MB1255-D-FA	\$197.00
ф160 mm (ф6.30 in.)	Three-Phase 230	MB1665-T	\$355.00	T-MB1665-T-A	\$375.00
	Single-Phase 110/115	MB1665-B	\$344.00	T-MB1665-B-A	\$364.00
	Single-Phase 220/230	MB1665-D	\$355.00	T-MB1665-D-A	\$375.00

Overview, **Product** Series

Axial Flow Fans

AC Input Low-Power Consumption EMU

AC Input Compact Size

AC Input Large Size, Large Air Flow MRS

AC Input Long-Life MRE

DC Input MDS MD

DC Input Alarm MDA

DC Input Variable Flow MDV

DC Input Long-Life MDE

DC Input Splash Proof MDP

DC Input MBD

Cross Flow Fans

AC Input MF DC Input MFD

Enclosure Fan Modules

Thermostat

Accessories

Installation

CAD Data Manuals

■Product line

MBD Series

◇No Additional Function

Impeller Diameter	Power Supply Voltage VDC	Fan Only		Fan Kit		
		Product Name	List Price	Product Name	List Price	
ф80 mm (ф3.15 in.)	24 MBD8-24	MDD0-24	\$91.00	T-MBD8-24-GA	\$105.00	
		MDD0-24		T-MBD8-24-FA	\$113.00	
	48 M	MBD8-48	\$96.00	T-MBD8-48-GA	\$110.00	
				T-MBD8-48-FA	\$118.00	
ф100 mm (ф3.94 in.)	24	MBD10-24	\$102.00	T-MBD10-24-GA	\$116.00	
				T-MBD10-24-FA	\$125.00	
	48	MBD10-48	\$107.00	T-MBD10-48-GA	\$121.00	
				T-MBD10-48-FA	\$130.00	
ф120 mm (ф4.72 in.)	24	MBD12-24	\$140.00	T-MBD12-24-GA	\$155.00	
	24			T-MBD12-24-FA	\$165.00	

\diamondsuit Low-Speed Alarm Type

Impeller Diameter	Power Supply Voltage VDC	Fan Only		Fan Kit		
		Product Name	List Price	Product Name	List Price	
ф80 mm (ф3.15 in.) ф100 mm (ф3.94 in.)	24	MBD8-24A	\$144.00	T-MBD8-24A-GA	\$158.00	
				T-MBD8-24A-FA	\$166.00	
		MBD10-24A	\$155.00	T-MBD10-24A-GA	\$169.00	
				T-MBD10-24A-FA	\$178.00	
ф120 mm (ф4.72 in.)		MBD12-24A	\$193.00	T-MBD12-24A-GA	\$208.00	
				T-MBD12-24A-FA	\$218.00	

For details (specifications, characteristics, dimensions and others) on these products please refer to either to our website, contact technical support or your nearest Oriental Motor sales office.