

Motor website.

**G-82** 



The **MDE** Series long-life axial flow fans utilize a brushless motor and have an expected life of 100,000 hours. A stall alarm comes standard.

These fans are available from  $\Box$ 60 mm ( $\Box$ 2.36 in.) to  $\phi$ 172 mm ( $\phi$ 6.77 in.) in frame sizes.



View Expanded Product Information, Specifications, CAD, Accessories & more online. Visit www.orientalmotor.com/catalog or use the QR code and select "**MDE** Series".

## Features

Long-Life

By using long life fans with an expected life of 100,000 hours (approximately 11 years), the maintenance interval can be extended, and the number of times the cooling fans are replaced can also be reduced. In addition to reducing running costs, this also reduces scrapped parts, which can contribute to both financial and environmental gains.


## Wide Variety of Products

|                | MDE625   | MDE825      | MDE925   | MDE1225   | MDE1238     | MDE1451   | MDE1751*  |
|----------------|--|-------------|--|---|-------------|---|---|
| Frame Size     | □60 mm-25 mm thick<br>(□2.36 in0.98 in. thick) |             | □92 mm-25 mm thick<br>(□3.62 in0.98 in. thick) | □119 mm-25.4 mm thick<br>(□4.69 in1.00 in. thick) |             | □140 mm-51 mm thick<br>(□5.51 in2.01 in. thick) | $\varphi 172$ mm-51 mm thick ( $\varphi 6.77$ in2.01 in. thick) |
| Alarm Type     | Stall Alarm                                    | Stall Alarm | Stall Alarm                                    | Stall Alarm                                       | Stall Alarm | Stall Alarm                                     | Stall Alarm   |
| Power 12 VDC   |  |             |  | •   |             |   |   |
| Supply 24 VDC  | •  | •           | •  | •   | •           | •   | •   |
| Voltage 48 VDC |  |             |  |   |             | •   |   |

\*Side-cut type is also available.

#### Fans with Stall Alarm

Outputs an alarm when the cooling fan stops. Quickly detects defective stops to allow the cooling fan to be replaced.



# Cooling Fans G-83

## System Configuration

|   | MDE Series         |               |         | quipment (Sold separately) | <b>wer Supply</b><br>ower supply)<br>d | Overview,<br>Product<br>Series<br>Axial<br>Flow<br>Fans<br>AC Input<br>Low-Power<br>Consumption<br>EMU |
|---|--------------------|---------------|---------|----------------------------|--|--|
| _ | - Accessories (Sol | d separately) |         | ]                          |  | AC Input<br>Compact Size<br><b>MU</b>  |
|   |                    |               |         |                            |  | AC Input<br>Large Size,<br>Large Air Flow<br><b>MRS</b>  |
|   |                    |               |         |                            |  | AC Input<br>Long-Life<br>MRE   |
|   | Finger Guards      | Filters       | Screens |                            |  | DC Input<br>MDS<br>MD  |
|   |                    |               |         |                            |  |  |

### Product Number

| Fan Only | ,  |    |   |        |
|----------|----|----|---|--------|
| MDE      | 17 | 51 | F | - 24 L |
| 1        | 2  | 3  | 4 | 56     |

| 1 | Series                  | MDE: MDE Series  | - Var     |
|---|-------------------------|--|-----------|
| 2 | Frame Size              | 6: 60 mm (2.36 in.), 8: 80 mm (3.15 in.), 9: 92 mm (3.62 in.),<br>12: 119 mm (4.69 in.), 14: 140 mm (5.51 in.),<br>17: ∲172 mm (∲6.77 in.) | DC        |
| 3 | Frame Thickness         | <b>25</b> : 25 mm (0.98 in.) or 25.4 mm (1.00 in.),<br><b>38</b> : 38 mm (1.50 in.), <b>51</b> : 51 mm (2.01 in.)                          | M         |
| 4 | Frame Shape             | F: Side-cut  | DC<br>Spl |
| 5 | Power Supply<br>Voltage | 12: 12 VDC, 24: 24 VDC, 48: 48 VDC   | M         |
| 6 | Additional Function     | L: Stall Alarm, Electronic Alarm Type  | _         |
|   |                         |  | Cen       |

| Fan        | Kit          |   |
|------------|--------------|---|
| <b>T</b> - | MDE1751F-24L | G |
| 1          | 2            | 3 |

| 1 | Fan Kit Order Code                               |
|---|--|
| 2 | Fan Product Name                                 |
| 3 | -G, G: With finger guard and installation screws |

### Product Line

| Size   | Power Supply Voltage | Fan Only     |            | Fan Kit         |            |
|--|----------------------|--------------|------------|-----------------|------------|
| SIZE   | VDC                  | Product Name | List Price | Product Name    | List Price |
| □60 mm - 25 mm Thick<br>(□2.36 in 0.98 in. Thick)  | 24                   | MDE625-24L   | \$84.00    | T-MDE625-24L-G  | \$88.00    |
| □80 mm - 25 mm Thick<br>(□3.15 in 0.98 in. Thick)  | 24                   | MDE825-24L   | \$84.00    | T-MDE825-24L-G  | \$89.00    |
| □92 mm - 25 mm Thick<br>(□3.62 in 0.98 in. Thick)  | 24                   | MDE925-24L   | \$84.00    | T-MDE925-24L-G  | \$90.00    |
| 119 mm - 25.4 mm Thick                             | 12                   | MDE1225-12L  | \$64.00    | T-MDE1225-12L-G | \$70.00    |
| ( 4.69 in 1.00 in. Thick)                          | 24                   | MDE1225-24L  | \$64.00    | T-MDE1225-24L-G | \$70.00    |
| □119 mm - 38 mm Thick<br>(□4.69 in 1.50 in. Thick) | 24                   | MDE1238-24L  | \$132.00   | T-MDE1238-24L-G | \$138.00   |
| □140 mm - 51 mm Thick                              | 24                   | MDE1451-24L2 | \$80.00    | T-MDE1451-24L2G | \$87.00    |
| ( 5.51 in 2.01 in. Thick)                          | 48                   | MDE1451-48L2 | \$80.00    | T-MDE1451-48L2G | \$87.00    |
| $\phi$ 172 mm - 51 mm Thick                        | 24                   | MDE1751-24L  | \$152.00   | T-MDE1751-24L-G | \$166.00   |
| (\$6.77 in 2.01 in. Thick)                         | 24                   | MDE1751F-24L | \$152.00   | T-MDE1751F-24LG | \$169.00   |



For details (specifications, characteristics, dimensions and others) on these products please refer to either to our website, contact technical support or your nearest Oriental Motor sales office.

www.orientalmotor.com/catalog

DC Input Alarm **MDA** 

DC Input Variable Flow **MDV** 

ng-l DE

C Input plash Proof **ADP** 

ntrifugal Blowers

> AC Input MB DC Input MBD

**Cross Flow Fans** 

AC Input MF DC Input MFD

Enclosure Fan Modules

Thermostat

Accessories

Installation