




TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED
OUT PUT	1/2 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
RATING	S1 CONT.
INS.CLASS	F

TYPE	GTR
FORM	30
RATIO	1/5 1/7.5 1/10 1/12.5
	1/15 1/20 1/25 1/30
	1/40 1/50 1/60
LUBRICATION	GREASE

TITLE		F3S30N5~60-MF4AEN DIMENSION OF MODEL			
DRAWING NO.		F3S30N-MF4AEN			
USER					
NOTICE					
APPROVE	Y. Ikeda	SCALE 1/5		UNIT	DATE
CHECK	M. Iijima			in	2015.07.15
DESIGN	Y. Miura			NISSEI CORPORATION	