




TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED P9
OUT PUT	3 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
EFFICIENCY CLASS	IE3 EN60034-30 Standard
RATING	S1 CONT.
INS.CLASS	F

TYPE	GTR
FORM	45
RATIO	1/5 1/7.5 1/10 1/12.5 1/15 1/20 1/25 1/30
LUBRICATION	GREASE

TITLE		F3S45N5~30-MV9AWN			
		DIMENSION OF MODEL			
DRAWING NO.		F3S45N-MV9AWN			
USER					
NOTICE					
APPROVE	Y.Ikeda	SCALE 1/6		UNIT	DATE
CHECK	M.Iijima			in	2016.04.01
DESIGN	Y.Miura			NISSEI CORPORATION	