


REVISIONS



TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED
OUT PUT	1/2 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
RATING	S1 CONT.
INS.CLASS	F

TYPE	GTR
FORM	28
RATIO	1/30 1/40 1/50 1/60 1/80
LUBRICATION	GREASE

TITLE		G3K28N30~80-MF4AEN			
		DIMENSION OF MODEL			
DRAWING NO.		G3K28N-MF4AEN			
USER					
NOTICE					
APPROVE	Y.Ikeda	SCALE 1/3		UNIT	DATE
CHECK	M.Iijima			in	2015.07.15
DESIGN	Y.Miura			NISSEI CORPORATION	

TITLE		G3K28N30~80-MF4AEN			
		DIMENSION OF MODEL			
DRAWING NO.		G3K28N-MF4AEN			
USER					
NOTICE					
APPROVE	Y.Ikeda	SCALE 1/3		UNIT	DATE
CHECK	M.Iijima			in	2015.07.15
DESIGN	Y.Miura			NISSEI CORPORATION	