


### MOTOR SPECIFICATION

TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED
OUT PUT	1/2 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
RATING	S1 CONT.
INS. CL ASS	F

## REDUCER SPECIFICATION

TYPE	GTR
FORM	28R
RATIO	1/5 1/10 1/15 1/20
	1/25 1/30 1/40 1/50
	1/60
LUBRICATION	GREASE

NOTE: THIS MOTOR IS AFFIXED WITH CE MARKING.  
NOTE: THE GROUND LEAD SHOULD BE LONGER THAN  
THE SUPPLY LEAD FOR THE MOTOR.  
NOTE: THIS MOTOR IS UL CERTIFIED MODEL.(UL1004-1)  
NOTE: UL-LISTED MODEL NAME: MF4AEN

TITLE		H2L28R5~60-MF4AEN DIMENSION OF MODEL			
DRAWING NO.		H2L28R-MF4AEN			
USER					
NOTICE					
APPROVE	Y.Ikeda	SCALE 1/3		UNIT	DATE
CHECK	M.Iijima			in	2015.07.15
DESIGN	Y.Miura			NISSEI CORPORATION	