


REVISIONS



TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED
OUT PUT	1/2 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
RATING	S1 CONT.
INS.CLASS	F

TYPE	GTR
FORM	32L
RATIO	1/80 1/100 1/120
	1/160 1/200 1/240
LUBRICATION	GREASE

TITLE		H2L32L80~240-MF4AEN			
		DIMENSION OF MODEL			
DRAWING NO.		H2L32L-MF4AEN			
USER					
NOTICE					
APPROVE	Y.Ikeda	SCALE 1/4		UNIT	DATE
CHECK	M.Iijima			in	2015.07.15
DESIGN	Y.Miura			NISSEI CORPORATION	