


REVISIONS



NOTE: OUTPUT SHAFT AND KEY MATERIAL: SUS420J2


## MOTOR SPECIFICATION

TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED P8
OUT PUT	2 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
EFFICIENCY CLASS	IE3 EN60034-30 Standard
RATING	S1 CONT.
INS.CLASS	F

## REDUCER SPECIFICATION

TYPE	GTR
FORM	40H
RATIO	1/5 1/10 1/15 1/20
	1/25 1/30 1/40 1/50
	1/60
LUBRICATION	GREASE

NOTE: UL—LISTED MODEL NAME: WV8AWN

TITLE		H2L40H5~60-WV8AWN		
		DIMENSION OF MODEL		
DRAWING NO.		H2L40H-WV8AWN		
USER				
NOTICE				
APPROVE	Y. Ikeda	SCALE 1/4		UNIT
CHECK	M. Iijima			in
DATE	Y. Miura			2016.04.01
DESIGN		NISSEI CORPORATION		