







DETAIL OF OUTPUT SHAFT



DETAIL OF : A



MOTOR SPECIFICATION

TYPE	1-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED TECA13
OUT PUT	1/2 HP
VOLTAGE	220 V
FREQ	50/60 Hz
POLES	4
RATING	S1 CONT.

REDUCER SPECIFICATION

TYPE	GTR
FORM	35
RATIO	1/80 1/100 1/120
	1/160 1/200 1/240
LUBRICATION	GREASE

NOTE: THIS MOTOR IS AFFIXED WITH CE MARKING.
NOTE: BE SURE TO USE THE THERMAL RELAY WITH
CE MARKING.
NOTE: THE GROUND LEAD SHOULD BE LONGER THAN
THE SUPPLY LEAD FOR THE MOTOR.
NOTE: INSULATION : CLASS A (UL) B (EN)
NOTE: THIS MOTOR IS UL CERTIFIED MODEL. (UL1004-1)
NOTE: UL-LISTED MODEL NAME: BML5S

TITLE		F3S35N080~240-BML5S			
		DIMENSION OF MODEL			
DRAWING NO. F3S35N-BML5S					
USER					
NOTICE					
APPROVE	Y.Ikeda	SCALE 1/6		UNIT	DATE
CHECK	I.Takashima			in	2014.12.05
DESIGN	T.Fujimoto			NISSEI CORPORATION	