




TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED
OUT PUT	3/4 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
RATING	S1 CONT.
INS.CLASS	F

TYPE	GTR
FORM	45
RATIO	1/80 1/100 1/120
	1/160 1/200 1/240
LUBRICATION	GREASE

TITLE						F3S45N80~240-MF5AWN					
DIMENSION OF MODEL											
DRAWING NO. F3S45N-MF5AWN											
USER											
NOTICE											
APPROVE	Y.Ikeda	SCALE 1/6		UNIT	DATE						
CHECK	Y.San ji			in	2016.10.16						
DESIGN	A.Kubota			NISSEI CORPORATION							