





MOTOR SPECIFICATION

TYPE	1-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED TECA13
OUT PUT	1/2 HP
VOLTAGE	220 V
FREQ	50/60 Hz
POLES	4
RATING	CONT.

REDUCER SPECIFICATION

TYPE	GTR
FORM	28
RATIO	1/30 1/40 1/50 1/60 1/80
LUBRICATION	GREASE

NOTE: THIS MOTOR IS AFFIXED WITH CE MARKING.
NOTE: BE SURE TO USE THE THERMAL RELAY WITH
CE MARKING.
NOTE: THE GROUND LEAD SHOULD BE LONGER THAN
THE SUPPLY LEAD FOR THE MOTOR.
NOTE: INSULATION : CLASS A
NOTE: THIS MOTOR IS UL CERTIFIED MODEL.(UL1004)
NOTE: UL—LISTED MODEL NAME: BML5S

TITLE					G3K28N030~080-BML5S	
					DIMENSION OF MODEL	
DRAWING NO. G3K28N-BML5S						
USER						
NOTICE						
APPROVE	K.Nagasaka	SCALE		UNIT in	DATE 2008.01.09	
CHECK	Y.Shiina					
DESIGN	M.Yoshida					
		1/4	NISSEI CORPORATION			