



REVISIONS



MOTOR SPECIFICATION

TYPE	1-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED TECA13
OUT PUT	1/2 HP
VOLTAGE	115 V
FREQ	50/60 Hz
POLES	4
RATING	CONT.

REDUCER SPECIFICATION

TYPE	GTR
FORM	28
RATIO	1/30 1/40 1/50 1/60 1/80
LUBRICATION	GREASE

NOTE: THIS MOTOR IS AFFIXED WITH CE MARKING.
 NOTE: BE SURE TO USE THE THERMAL RELAY WITH
 CE MARKING.
 NOTE: THE GROUND LEAD SHOULD BE LONGER THAN
 THE SUPPLY LEAD FOR THE MOTOR.
 NOTE: INSULATION : CLASS A
 NOTE: THIS MOTOR IS UL CERTIFIED MODEL.(UL1004)
 NOTE: UL-LISTED MODEL NAME: BML1S

TITLE					G3L28N030~080-BML1S	
DIMENSION OF MODEL						
DRAWING NO. G3L28N-BML1S						
USER						
NOTICE						
APPROVE	K.Nagasaka	SCALE		UNIT	DATE	
CHECK	Y.Shiina	1/4		in	2008.01.09	
DESIGN	M.Yoshida			NISSEI CORPORATION		