







NOTE: THE RATING OF ENCLOSURE CLASS:
IP65 (EN60034-5) EQUIVALENT.
NOTE: OUTPUT SHAFT MATERIAL: SUS420J2

MOTOR SPECIFICATION

TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED P9
OUT PUT	3 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
EFFICIENCY CLASS	IE3 EN60034-30 Standard
RATING	S1 CONT.
INS.CLASS	F

REDUCER SPECIFICATION

TYPE	GTR
FORM	50
RATIO	1/40 1/50 1/60
LUBRICATION	GREASE

NOTE: FIX THE PROTECTIVE COVER (ACCESSORY)
ON M4 (3 HOLES) USE ROUND-HEAD SCREWS
(ACCESSORY, 3PCE)

NOTE: THIS MOTOR IS AFFIXED WITH CE MARKING.

NOTE: THE GROUND LEAD SHOULD BE LONGER THAN
THE SUPPLY LEAD FOR THE MOTOR.

NOTE: THIS MOTOR IS UL CERTIFIED MODEL. (UL1004-1)

NOTE: UL-LISTED MODEL NAME: WV9AEN

TITLE		F3S50S40~60-WV9AEN			
		DIMENSION OF MODEL			
DRAWING NO.		F3S50S-WV9AEN			
USER					
NOTICE					
APPROVE	Y. Ikeda	SCALE 1/7		UNIT	DATE
CHECK	M. Iijima			in	2015.05.01
DESIGN	Y. Miura			NISSEI CORPORATION	