



モータ仕様 MOTOR SPECIFICATION	
名称 TYPE	三相誘導電動機 THREE PHASE INDUCTION MOTOR
冷却方式 COOLING METHOD	全閉外扇形 TOTALLY ENCLOSED FAN COOLED
出力 MOTOR POWER	3/4 HP (0.55 kW)
定格 RATING	S1 CONT.
耐熱 INS. CLASS	F
保護構造 IP RATING	IP44

**	電圧 VOLTAGE	周波数 FREQUENCY	回転速度 ROTATION SPEED	電流値 CURRENT VALUE	対応規格 COMPLIANT STANDARDS	高効率認証 EFFICIENCY STANDARDS	
AV	208 V 230 V 460 V 400 V	60 Hz 60 Hz 60 Hz 50 Hz	1700 r/min 1720 r/min 1720 r/min 1410 r/min	2.3 A 2.2 A 1.10 A 1.30 A	UL/cUL/CE	-	
EV	415 V 440 V 480 V	50 Hz 50 Hz 60 Hz	1410 r/min 1420 r/min 1720 r/min	1.25 A 1.20 A 1.10 A			
MA	575 V	60 Hz	1720 r/min	0.9 A			UL/cUL

減速機仕様 REDUCER SPECIFICATION	
名称 TYPE	GTR
枠番 FRAME NO.	32
減速比 RATIO	5 10 15 20 25 30 40 50 60
潤滑 LUBRICATION	グリース GREASE
塗装 PAINT COLOR	グレー (マンセル値 9B6/0.5) GREY (MANSEL CODE: 9B6/0.5)

出力軸仕様 OUTPUT SHAFT SPECIFICATION							
FRAME NO.	R	STANDARD /OPTION	DIAMETER TOLERANCE	L1	L2	T	W
32	1.2500 in	STANDARD	+0.0/-0.0005	1.88 in	2.00 in	1.362 in	0.2500 in
	32 mm	OPTION	+0.0/-0.016	50 mm	50 mm	35 mm	10 mm

- 製品型式「□□□」は減速比によって入る文字数が変わります。  
Number of characters on product model「□□□」varies depending on the reduction ratio.
- 製品型式「\*\*」には「AV」「EV」「MA」が入ります。  
Replace product model「\*\*」with「AV」「EV」「MA」.

TITLE	H2L32T□□□□-MB05T* *EN				
	外形寸法図 DIMENSION OF MODEL				
DRAWING NO.	H2L32T-MB05TEN				
USER					
NOTICE					
APPROVE	M.Iijima	SCALE	1:4	UNIT in	
CHECK	T.Fujie				DATE 2020.04.30
DESIGN	K.Miyachi				
			NISSEI CORPORATION		