



Standard AC Motors



Overview, Product Series.....	C-2
Constant Speed Motors.....	C-9
Three-Phase Induction Motors.....	C-21
Single-Phase Induction Motors.....	C-113
Reversible Motors.....	C-147
Electromagnetic Brake Motors.....	C-155
Clutch & Brake Motors.....	C-163
Low-Speed Synchronous Motors.....	C-167
Torque Motors.....	C-171
Watertight, Dust-Resistant Motors.....	C-177
Right-Angle Gearheads.....	C-181
Linear Heads.....	C-185
Brake Pack.....	C-191
Accessories.....	C-195
Installation.....	C-209

Overview,
Product
Series

Constant
Speed
Motors

Three-Phase
Induction
Motors

Single-Phase
Induction
Motors

Reversible
Motors

Electromagnetic
Brake Motors

Clutch &
Brake Motors

Low-Speed
Synchronous
Motors

Torque
Motors

Watertight,
Dust-Resistant
Motors

Right-Angle
Gearheads

Linear
Heads

Brake Pack


Accessories

Installation

Product Series of Standard AC Motors


A wide range of standard AC motors with different features to meet the demand for many applications.

Constant Speed Motors




Torque Motors

→ Page C-171




Watertight, Dust-Resistant Motors

→ Page C-177




Clutch & Brake Motors

→ Page C-163



Low-Speed Synchronous Motors

→ Page C-167



Overview of Standard AC Motors

Standard AC motors are used generally as a power source for automated equipment, because these motors can be operated easily by connecting the motors directly to an AC power supply.

Oriental Motor offers standard AC motors incorporating various operating functions. A standard AC motor supports various applications by using with a brake pack or speed control circuit product, and combining with other mechanical components such as a gearhead or linear head.


Features

Easy Operation


Standard AC motors include three-phase motors used with a three-phase power supply and single-phase motors used with a single-phase power supply.

A three-phase motor does not require a capacitor. All you need is to connect the motor directly to a three-phase power supply.

A single-phase motor can be operated simply by connecting it to a single-phase power supply via the supplied capacitor.



Induction Motors: Connection example for three-phase power supply input type



Induction Motors: Connection example for single-phase power supply input type

The Power Supply Frequency Determines the Speed

The basic speed (synchronous speed*) of a standard AC motor is determined by the power supply frequency and the number of poles. Many of our standard AC motors have four poles, so their synchronous speed is as follows:

- 50 Hz: 1500 r/min
- 60 Hz: 1800 r/min

The actual speed varies according to the load torque.

With our motors, the speed roughly falls within the following ranges at a load torque equivalent to the rated torque:

- 50 Hz: 1200 to 1300 r/min
- 60 Hz: 1450 to 1600 r/min

The rated speed of our standard AC motors are set within the above ranges and showed on each motor's specification page.


To calculate a more accurate machine speed, use the rated speed as a reference.

The power supply frequency varies from region to region. In the case of automated equipment used in different regions, change the gear ratio of the gearhead or take other appropriate measure to obtain the desired speed.

An Optimal Motor can be Selected According to the Load Torque

The torque generated by each standard AC motor is different depending on the motor frame size and length.

Oriental Motor offers standard AC motors with a frame size of 42 mm to 104 mm (1.65 in. to 4.09 in.) and output of 1 W to 200 W (1/750 HP to 1/4 HP). Select the optimal motor from the wide-ranging variations according to the load torque.



Speed - Torque Characteristics

*The synchronous speed is calculated by the formula below.

$$N_s = \frac{120 \times f}{P}$$

N_s : Synchronous Speed [r/min]

f : Power Supply Frequency [Hz]

P : Number of Poles (Many of our motors have four poles.)

Overview, Product Series

Constant Speed Motors

Three-Phase Induction Motors

Single-Phase Induction Motors

Reversible Motors

Electromagnetic Brake Motors

Clutch & Brake Motors

Low-Speed Synchronous Motors

Torque Motors

Watertight, Dust-Resistant Motors

Right-Angle Gearheads

Linear Heads

Brake Pack

Accessories

Installation


Product Line

Motors

A wide range of standard AC motors with different features to meet the demand for many applications.


Three-Phase Induction Motors

These new high-efficiency three-phase induction motors were created through optimized motor design.




Single-Phase Induction Motors

These motors can easily be operated from an AC power supply.




Reversible Motors

These motors generate a greater starting torque and have a built-in friction brake. These single-phase motors also allow for instantaneous switching of rotation direction.




Electromagnetic Brake Motors

These motors have a “power off” activated type electromagnetic brake to hold the load in position when the power is cut off.




Clutch & Brake (C·B) Motors

These motors are equipped with an electromagnetic clutch and brake at the motor output shaft. High frequency starting and stopping is possible while the motor is operating.




Low-Speed Synchronous Motors

These motors use the same stator and rotor as stepper motors. These motors offer superb starting, stopping and reversing characteristics as well as synchronous operation.




Watertight, Dust-Resistant Motors

These motors are watertight, dust-resistant and conform to the IEC Standard IP67.



Torque Motors

A special rotor is used to provide large starting torque and sloping characteristics (torque is highest at zero speed and decreases steadily with increasing speed). The torque can be changed by changing the applied voltage.



● Various Gearheads are Available for Assembly with Motors

Various gearheads that convert the speed and torque of a standard AC motor to the speed or torque required by automated equipment, as well as linear heads that convert motor rotation to linear motion.


Since standard AC motors are designed with a standard flange mounting surface, the desired gearhead can be assembled according to the specific application.

Note

- Available gearheads vary depending on the motor type.
- Not all gearheads are compatible. For details, check the pages where each product is listed.


Parallel Shaft Gearheads

The gear shaft is positioned in the same direction as (in parallel with) the motor shaft. Decimal gearheads are also available.




Right-Angle Gearheads

The gear shaft is positioned at right angles (90°) with the motor shaft. Solid shaft and hollow shaft types are available.



Linear Heads

The motor rotation is converted to linear motion using a rack-and-pinion mechanism. Both horizontal and vertical types are available.



● Various Control Circuits are Available for Use with Standard AC Motors


Using a standard AC motor with a control circuit suppresses overrun and enables variable speed operation.

Note

- Not all control circuits are compatible depending on the motor type, applicable voltage, etc.
- We also have many package models combining a control circuit with a motor.
- For details, check the pages where each product is listed.

Brake Pack


Upon receipt of a command from a programmable controller etc., a large braking current from the brake pack stops the motor instantaneously.



AC Speed Control Motors


When Combined with a Tachogenerator

A dedicated AC motor systems assembled with a tachogenerator is driven with a speed controller. Speed can be set with the speed controller's internal speed potentiometer or by using an external speed potentiometer.



When Combined with a Three-Phase Motor

Combined use of a speed controller with a three-phase induction motor enables motor operation at variable speed. Speed is set with the speed controller's internal speed potentiometer or by using an external DC voltage.



Overview, Product Series

Constant Speed Motors

Three-Phase Induction Motors

Single-Phase Induction Motors

Reversible Motors

Electromagnetic Brake Motors

Clutch & Brake Motors

Low-Speed Synchronous Motors

Torque Motors

Watertight, Dust-Resistant Motors

Right-Angle Gearheads

Linear Heads

Brake Pack

Accessories

Installation

Applications and Classifications

Constant Speed Motors

→ Page C-9

Three-Phase Induction Motors


→ Page C-21



They are suitable for applications where speed control will be performed in combination with an inverter.

Single-Phase Induction Motors


→ Page C-113



Suitable for applications where the motor is operated continuously in one direction.

For Bi-Directional Operation Reversible Motors


→ Page C-147



Suitable for applications where the motor reverses its direction repeatedly.

For Load Holding Electromagnetic Brake Motors


→ Page C-155



Suitable for applications where the load must always be held in place.

For High-Frequency Start and Stop Operation Clutch and Brake Motors


→ Page C-163



Ideal for high-frequency starting and stopping.

For Synchronous Rotation Low-Speed Synchronous Motors


→ Page C-167



Suitable for applications where the motor is operated starting, stopping and reversing repeatedly and the motor is operated at synchronous speed regardless of load torque.

Watertight, Dust-Resistant Motors


→ Page C-177



Suitable for applications where the equipment comes in contact with water or needs to be washed with water.

Torque Motors

→ Page C-171




Suitable for winding and other operations involving tension control, as well as pushing operations.

Gearheads

Parallel Shaft Gearheads


→ Refer to the page of each motor.



Installing a parallel shaft gearhead on a pinion shaft type motor allows the motor to reduce the speed and generate greater torque.

Right-Angle Gearheads


→ Page C-181



Suitable for applications where space saving is required.

Linear Motion Linear Heads


→ Page C-185



Linear motion can be achieved easily by installing a linear head on a pinion shaft type motor.

Instantaneous Stop Brake Pack

→ Page C-191



Suitable for applications where the overrun of an induction motor, reversible motor or electromagnetic brake motor should be suppressed.

Accessories

→ Page C-195




Various accessories are available that can be combined effectively with motors and gearheads. Selection is easy once you know which motor product you will be using.

Brushless Motors/AC Speed Control Motors

→ Page D-1

Brushless Motors


→ Page D-11



Suitable for applications where a wide speed control range is required.

AC Speed Control Motors

→ Page D-135



Suitable for applications where the motor speed needs to be varied.

Overview,
Product
Series

Constant
Speed
Motors

Three-Phase
Induction
Motors

Single-Phase
Induction
Motors

Reversible
Motors

Electromagnetic
Brake Motors

Clutch &
Brake Motors

Low-Speed
Synchronous
Motors

Torque
Motors

Watertight,
Dust-Resistant
Motors

Right-Angle
Gearheads

Linear
Heads

Brake Pack

Accessories

Installation

