




DETAIL OF : A

BRAKE SPECIFICATION

TYPE	BS3-22-180
BRAKE TYPE	SPRING CLOSE
INPUT VOLTAGE	DC 207V
POWER CONSUMPTION	49 W (at 75°C)
BRAKE TORQUE	152.7 in-lbs



NOTE: THE BRAKE LEADS ARE PULLED INTO THE TERMINAL BOX.

NOTE: THE ATTACHED RECTIFIER IS USED FOR
DC POWER SUPPLY TO THE BRAKE COIL.

MOTOR SPECIFICATION

TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED P9
OUT PUT	3 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
EFFICIENCY CLASS	IE3 EN60034-30 Standard
RATING	S1 CONT.
INS.CLASS	F

REDUCER SPECIFICATION

TYPE	GTR
FORM	50
RATIO	1/40 1/50 1/60
LUBRICATION	GREASE

NOTE: COMPLIANCE CERTIFICATION NUMBER: CC303B

NOTE: FIX THE PROTECTIVE COVER (ACCESSORY)

ON M4 (3 HOLES) USE ROUND-HEAD SCREWS
(ACCESSORY, 3PCE)

NOTE: THIS MOTOR IS AFFIXED WITH CE MARKING.

NOTE: THE GROUND LEAD SHOULD BE LONGER THAN THE SUPPLY LEAD FOR THE MOTOR.

NOTE: THIS MOTOR IS UL CERTIFIED MODEL. (UL1004-1)

NOTE: UL—LISTED MODEL NAME: MV9AWB4

TITLE						F3S50N40~60-MV9AWB4	
						DIMENSION OF MODEL	
DRAWING NO.			F3S50N-MV9AWB4				
USER							
NOTICE							
APPROVE	Y.Ikeda	SCALE 1/7		UNIT	DATE		
CHECK	M.Iijima			in	2016.04.01		
DESIGN	Y.Miura			NISSEI CORPORATION			