





MOTOR SPECIFICATION

TYPE	1-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED TECA13
OUT PUT	1/2 HP
VOLTAGE	115 V
FREQ	50/60 Hz
POLES	4
RATING	CONT.

REDUCER SPECIFICATION

TYPE	GTR
FORM	22
RATIO	1/5 1/10 1/15 1/20 1/25
LUBRICATION	GREASE

NOTE: THIS MOTOR IS AFFIXED WITH CE MARKING.
NOTE: BE SURE TO USE THE THERMAL RELAY WITH
CE MARKING.
NOTE: THE GROUND LEAD SHOULD BE LONGER THAN
THE SUPPLY LEAD FOR THE MOTOR.
NOTE: INSULATION : CLASS A
NOTE: THIS MOTOR IS UL CERTIFIED MODEL.(UL1004)
NOTE: UL-LISTED MODEL NAME: BML1S

TITLE					G3K22N005~025-BML1S				
					DIMENSION OF MODEL				
DRAWING NO. G3K22N-BML1S									
USER									
NOTICE									
APPROVE	K.Nagasaka			SCALE		UNIT	DATE		
CHECK	Y.Shiina			1/3		in	2008.01.09		
DESIGN	M.Yoshida								
					NISSEI CORPORATION				