




NOTE: THE ATTACHED RECTIFIER IS USED FOR
DC POWER SUPPLY TO THE BRAKE COIL.

TITLE					G3K28N5~25-MV6AWB2	
					DIMENSION OF MODEL	
DRAWING NO.			G3K28N-MV6AWB2			
USER						
NOTICE						
APPROVE	Y.Ikeda	SCALE 1/3		UNIT	DATE	
CHECK	M.Iijima			in	2016.04.01	
DESIGN	Y.Miura			NISSEI CORPORATION		

TYPE	BS3-08
BRAKE TYPE	SPRING CLOSE
INPUT VOLTAGE	DC 104V
POWER CONSUMPTION	33 W (at 75°C)
BRAKE TORQUE	52.0 in-lbs

TYPE	3-PHASE INDUCTION MOTOR
FORM	TOTALLY ENCLOSED FAN COOLED P6
OUT PUT	1 HP
VOLTAGE	208/230/460/400 V
FREQ.	60/60/60/50 Hz
POLES	4
ROTATIONAL FREQUENCY	1800/1800/1800/1500 rpm
EFFICIENCY CLASS	IE3 EN60034-30 Standard
RATING	S1 CONT.
INS.CLASS	F

TYPE	GTR
FORM	28
RATIO	1/5 1/10 1/15 1/20 1/25
LUBRICATION	GREASE