Oriental motor



HM-60360-2

OPERATING MANUAL

2-Phase Stepping Motor

PKP Series Flat Type

Before use

Introduction

Only qualified personnel of electrical and mechanical engineering should work with the product.

Use the product correctly after thoroughly reading the "Safety precautions" In addition, be sure to observe the contents described in warning, caution, and note in this manual. The product described in this manual has been designed and manufactured to be incorporated in general industrial equipment. Do not use for any other purpose. Oriental Motor Co., Ltd. is not responsible for any damage caused through failure to observe this warning.

Safety precautions

The precautions described below are intended to prevent danger or injury to the user and other personnel through safe, correct use of the product. Use the product only after carefully reading and fully understanding these instructions.

Description of signs

	Handling the product without observing the instructions tha accompany a "WARNING" symbol may result in serious injury or death.
	Handling the product without observing the instructions that accompany a "CAUTION" symbol may result in injury or property damage.
Note	The items under this heading contain important handling instructions that the user should observe to ensure the safe use of the product.

Description of graphic symbols

Indicates "prohibited" actions that must not be performed.

Indicates "compulsory" actions that must be performed.

\bigcirc	 Do not use the product in explosive or corrosive environments, in the presence of flammable gases, locations subjected to splashing water, or near combustibles. Doing so may result in fire or injury. Do not forcibly bend, pull or pinch the lead wires and connector. Doing so may result in fire. Do not disassemble or modify the product. Doing so may result in injury.
0	 Assign qualified personnel to the task of installing, wiring, operating/ controlling, inspecting and troubleshooting the product. Failure to do so may result in fire or injury. Take measures to keep the moving part in position if the product is used in vertical operations such as elevating equipment. Failure to do so may result in injury or damage to equipment. Install the product inside an enclosure. Failure to do so may result in injury. Connect the lead wires securely according to the wiring diagram. Failure to do so may result in fire.

Thank you for purchasing an Oriental Motor product.

This Operating Manual describes product handling procedures and safety precautions. · Please read it thoroughly to ensure safe operation.

Always keep the manual where it is readily available.



Precautions for use

that

• When conducting the insulation resistance measurement or the dielectric strength test, be sure to separate the connection between the motor and the driver.

Conducting the insulation resistance measurement or dielectric strength test with the motor and driver connected may result in damage to the product.

 Do not apply a radial load and axial load in excess of the specified permissible limit

Operating the motor under an excessive radial load or axial load may damage the bearings (ball bearings). Be sure to operate the motor within the specified permissible limit of radial load and axial load.

Motor surface temperature

The motor surface temperature may exceed 100 °C (212 °F) under certain conditions (operating ambient temperature, operating speed, duty cycle, etc.). To prevent the bearings (ball bearings) from reaching its usable life quickly, use the motor in conditions where the surface temperature does not exceed 100 °C (212 °F). Use the geared motor in a condition where the gear case temperature does not exceed

70 °C (158 °F), in order to prevent deterioration of grease and parts in the gear case.

Rotation direction of output flange of Harmonic geared type

The output flange of the Harmonic geared type rotates in the opposite direction to the rotation direction of the motor output shaft.

Preparation

Checking the product

Verify that the items listed below are included. Report any missing or damaged items to the Oriental Motor sales office from which you purchased the product.

- 1 unit Motor
- OPERATING MANUAL 1 copy (this document)

Model list

Verify the model number of the purchased motor against the number shown on the nameplate.

Туре	Motor frame size [mm (in.)]	Gear ratio	Motor model
Standard	42 (1.65)	-	PKP242D23A2
Stanuaru	60 (2.36)	-	PKP262FD15AW
	51 (2.01)	50	PKP242D23A2-H50
Harmonic geared	51 (2.01)	100	PKP242D23A2-H100
	61 (2.40)	50	PKP262FD15AW-H50S
	61 (2.40)	100	PKP262FD15AW-H100S

Information about nameplate

The figure shows an example.



(memo) The position describing the information may vary depending on the product.

Names of parts

Connector type

The pin numbers as well as the colors of lead wires are shown in the figures.

Connector

Pin No.1

holes (2 places)

Standard type

Output

shaft

Motor frame size: 42 mm (1.65 in.)

Pin No.5

Pilot

 Harmonic geared type Motor frame size: 51 mm (2.01 in.) The area indicated in gray color represents



Wiring connection diagram (Bipolar four lead wires)

The connection diagrams show our connection cable. (The pin No.3 is not used.)



А

1/Black o

Connection cable



Applicable connector/lead wire

Туре	Model
Connector housing	MDF97-5S-3.5C (HIROSE ELECTRIC CO., LTD.)
Contact	MDF97-22SC (HIROSE ELECTRIC CO., LTD.)
Designated crimping tool	HT801/MDF97-22S (HIROSE ELECTRIC CO., LTD.)
Applicable lead wire	AWG24 to 22 (0.2 to 0.3 mm ²) Outer sheath diameter: ø1.24 to 1.38 mm (0.049 to 0.054 in.) Stripping length of wire insulation: 1.8 to 2.3 mm (0.071 to 0.091 in.)

• Lead wire type

 Standard type Motor frame size: 60 mm (2.36 in.)



Harmonic geared type

Motor frame size: 61 mm (2.40 in.) The area indicated in gray color represents a rotating part.



Wiring connection diagram (Bipolar four lead wires)

Green В Red Blue

Specifications of drivers possible to combine

Use the 2-phase stepping motor flat type in combination with drivers which specifications are described in the table. The box (\Box) in the model name indicates the gear ratio.

• Driver with mounting plate

Motor model	Driver model		Motor rated
Motor moder	Right angle		current
PKP242D23A2	CVD223FBR-K	CVD223FB-K	22 A/phase
PKP242D23A2-H	CVD223FBR-K	CVD223FB-K	2.5 A/phase
PKP262FD15AW	CVD215BR-K	CVD215B-K	
PKP262FD15AW-HDS	CVD215BR-K	CVD215B-K	1.5 A/phase

• Driver without mounting plate

Motor model	Driver model	Motor rated current
PKP242D23A2	CVD223F-K	22 A/phase
PKP242D23A2-H	CVD223F-K	2.5 A/phase
PKP262FD15AW	CVD215-K	154/abaaa
PKP262FD15AW-HDS	CVD215-K	1.5 A/phase

Connection

When inserting the connector

Hold the connector main body, and insert it in straight securely. Inserting the connector in an inclined state may result in damage to connector or a connection failure.

• When unplugging the connector

Pull out the connector in straight while releasing the lock part of the connector. Having the motor lead wires or pulling out the connector in a state of being locked may damage the connector.



Note

Secure the lead wires at the connection part to prevent the connection part from receiving stress due to the flexing of the lead wires or the lead wires' own mass. Also, do not excessively bend the lead wires near the connection part of the connector. Applying stress on the motor lead wires may cause poor contact or disconnection, leading to malfunction or heat generation.



Connection with the drivers of Oriental Motor

Refer to the following table when connecting with the drivers of Oriental Motor. "Color" in the table shows the colors of lead wires of our connection cable.

• Connection with the CVD Series

Driver	Connec	tor type	Lead wire type
CN2 Pin No.	Pin No. Color		Color
1	4	Blue	Blue
2	5	Red	Red
3	-		-
4	2	Green	Green
5	1	Black	Black

Installation

Location for installation

The motor is designed and manufactured to be incorporated in equipment. Install it in a well-ventilated location that provides easy access for inspection.

The location must also satisfy the following conditions:

- Inside an enclosure that is installed indoors (provide vent holes)
- Operating ambient temperature
- -10 to +50 °C (+14 to +122 °F) (non-freezing)
- Harmonic geared type: 0 to +40 $^{\circ}$ C (+32 to +104 $^{\circ}$ F) (non-freezing)
- Operating ambient humidity 85% or less (non-condensing)
- Area that is free of explosive atmosphere or toxic gas (such as sulfuric gas) or liquid
 Area not exposed to direct sun
- Area free of excessive amount of dust, iron particles or the like
- Area not subject to splashing water (rain, water droplets), oil (oil droplets), or other liquids
- Area free of excessive salt
- Area not subject to continuous vibration or excessive shocks
- Area free of excessive electromagnetic noise (from welders, power machinery, etc.)
- Area free of radioactive materials, magnetic fields or vacuum
- 1,000 m (3,300 ft.) or lower above sea level

Installation method

The motor can be installed in any direction. Install the motor onto an appropriate flat metal plate having excellent vibration resistance and heat conductivity.

When installing the motor, secure it with screws (not included) so that there is no gap between the motor and metal plate.

Standard type

Motor frame size: 42 mm (1.65 in.) Motor frame size: 60 mm (2.36 in.)



Motor frame size [mm (in.)]	Nominal size	Tightening torque [N·m (oz-in)]	Effective depth of screw thread [mm (in.)]
42 (1.65)	M3	1 (142)	4.5 (0.18)
60 (2.36)	M4	2 (280)	-

Harmonic geared type

Motor frame size: 51 mm (2.01 in.)

Motor frame size: 61 mm (2.40 in.)



Motor frame size [mm (in.)]	Nominal size	Tightening torque [N·m (oz-in)]	Effective depth of screw thread [mm (in.)]
51 (2.01)	M3	1 (142)	7 (0.28)
61 (2.40)	M4	2 (280)	-

Installing a load

When installing a load to the motor, align the centers of the motor output shaft and load shaft. Be careful not to damage the output shaft or bearings (ball bearings) when installing a coupling or pulley to the motor output shaft.

Harmonic geared type

Install a load using the load mounting screw holes.



Load mounting screw hole

Motor frame size [mm (in.)]	Nominal size	Tightening torque [N·m (oz-in)]	Effective depth of screw thread [mm (in.)]
51 (2.01)	M3	2.0 (280)	6 (0.24)
61 (2.40)	M4	4.5 (630)	5 (0.20)



Since the tightening torque for the load mounting screw is large, using a mechanically weak load or screws may cause damage. Satisfy the following conditions for the load and mounting screws. Also, be sure to tighten with the specified torque.

. Material of load: Steel

Mounting screw: Use a bolt which tensile strength ranking is 12.9 or higher

Permissible radial load, permissible axial load, and permissible moment load

The radial load, axial load, and moment load on the motor output shaft must be kept under the permissible values in the table.

Standard type

	Permiss	ible radial load	[N (lb.)]	
Motor frame size [mm (in.)]	Distance from the tip of motor output shaft [mm (in.)]			Permissible axial load [N (lb.)]
	0 (0)	5 (0.2)	10 (0.39)	[11 (121)]
42 (1.65), 60 (2.36)	20 (4.5)	25 (5.6)	34 (7.6)	5 (1.12)

• Harmonic geared type

Calculate the axial load and load moment for the Harmonic geared type using the International System of Units (N, N $\cdot m$).

Motor frame size [mm (in.)]	Permissible axial load [N]	Permissible moment load [N·m]
51 (2.01)	200	8.5
61 (2.40)	450	10.1

How to calculate loads of Harmonic geared type

Use the calculating formula below for the axial load and moment load of Harmonic geared type.

Example 1; When an external force F is applied on the position of distance L from the center of the output flange

Axial load: Fs [N] = F + mg (Load mass) Moment load: ΔM [N·m] = F × L



Example 2; When external forces F1 and F2 are applied on the position of distance L from the mounting face of the output flange

Axial load: Fs [N] = F1 + mg (Load mass)

Moment load: $\Delta M [N \cdot m] = F2 \times (L + constant a)$

- * Motor frame size 51 mm (2.01 in.): constant a = 0.0129 [m]
- Motor frame size 61 mm (2.40 in.): constant a = 0.0140 [m]



Inspection and maintenance

Inspection

It is recommended that periodic inspections would be conducted for the items listed below after each operation of the motor. If an abnormal condition is noted, discontinue any use and contact your nearest Oriental Motor sales office.

Inspection item

- Check if any of the screws having installed the motor comes loose.
- Check if an unusual noise or vibration is generated from a bearing part (ball bearings).
- Check if a damage or stress is applied on the motor lead wires.
- Check if the connection part with the connector or the driver comes loose.
- Check if the motor output shaft and the load shaft are out of alignment.

Warranty

Check on the Oriental Motor Website or General Catalog for the product warranty.

Disposal

Dispose the product correctly in accordance with laws and regulations, or instructions of local governments.

Specifications

Check on the Oriental Motor Website for the product specifications.

General specifications

Degree of protection		protection	IP20
	Operation environment	Ambient temperature	-10 to +50 °C (+14 to +122 °F) (non-freezing) Harmonic geared type: 0 to +40 °C (+32 to +104 °F) (non-freezing)
		Humidity	85% or less (non-condensing)
		Altitude	Up to 1,000 m (3,300 ft.) above sea level
		Surrounding atmosphere	No corrosive gas, dust, water or oil
	Storage environment Shipping environment	Ambient temperature	-20 to +60 °C (-4 to +140 °F) (non-freezing)
		Humidity	85% or less (non-condensing)
		Altitude	Up to 3,000 m (10,000 ft.) above sea level
		Surrounding atmosphere	No corrosive gas, dust, water or oil
	Insulation resistance	100 $M\Omega$ or more when 500 VDC megger is applied between the windings and the case.	
	Dielectric strength	Sufficient to withstand the following conditions applied between th windings and the case for 1 minute. • 0.5 kVAC 50/60 Hz	

Regulations and standards

RoHS Directive

The products do not contain the substances exceeding the restriction values of RoHS Directive (2011/65/EU).

- Unauthorized reproduction or copying of all or part of this manual is prohibited.
- Oriental Motor shall not be liable whatsoever for any problems relating to industrial property rights arising from use of any information, circuit, equipment or device provided or referenced in this manual.
- Characteristics, specifications and dimensions are subject to change without notice.
- While we make every effort to offer accurate information in the manual, we welcome your input. Should you find unclear descriptions, errors or omissions, please contact your nearest Oriental Motor sales office.
- **Oriental motor** is a registered trademark or trademark of Oriental Motor Co., Ltd., in Japan and other countries.

© Copyright ORIENTAL MOTOR CO., LTD. 2018

Published in July 2021

• Please contact your nearest Oriental Motor office for further information.

ORIENTAL MOTOR U.S.A. CORP. Technical Support Tel:800-468-3982 8:30am EST to 5:00pm PST (M-F) www.orientalmotor.com ORIENTAL MOTOR (FUROPA) GmbH

ORIENTAL MOTOR (EUROPA) GmbH Schiesstraße 44, 40549 Düsseldorf, Germany Technical Support Tel:00 800/22 55 66 22 www.orientalmotor.de ORIENTAL MOTOR (UK) LTD. Unit 5 Faraday Office Park, Rankine Road, Basingstoke, Hampshire RG24 8QB UK Tel:+44-1256347090 www.oriental-motor.co.uk ORIENTAL MOTOR (FRANCE) SARL Tel:+33-1 47 86 97 50 www.orientalmotor.fr ORIENTAL MOTOR ITALIA s.r.I. Tel:+39-02-93906347 www.orientalmotor.it ORIENTAL MOTOR CO., LTD. 4-8-1Higashiueno,Taito-ku,Tokyo 110-8536 Japan

Tel:+81-3-6744-0361 www.orientalmotor.co.jp ORIENTAL MOTOR ASIA PACIFIC PTE. LTD. Singapore Tel:1800-842-0280 www.orientalmotor.com.sg ORIENTAL MOTOR (MALAYSIA) SDN, BHD, Tel:1800-806-161 www.orientalmotor.com.my ORIENTAL MOTOR (THAILAND) CO., LTD. Tel:1800-888-881 www.orientalmotor.co.th ORIENTAL MOTOR (INDIA) PVT. LTD. Tel:1800-120-1995 (For English) 1800-121-4149 (For Hindi) www.orientalmotor.co.in TAIWAN ORIENTAL MOTOR CO., LTD. Tel:0800-060708 www.orientalmotor.com.tw SHANGHAI ORIENTAL MOTOR CO., LTD. Tel:400-820-6516 www.orientalmotor.com.cn INA ORIENTAL MOTOR CO., LTD. Korea Tel:080-777-2042 www.inaom.co.ki