# **O**riental motor



#### HM-7443-9

### **OPERATING MANUAL**

### 2-Phase Stepping Motor

**PKP** Series

### Introduction

### Before use

Only qualified personnel of electrical and mechanical engineering should work with the product.

Use the product correctly after thoroughly reading the "Safety precautions." In addition, be sure to observe the contents described in warning, caution, and note in this manual. The product described in this manual is designed and manufactured to be incorporated in general industrial equipment. Do not use for any other purpose. Oriental Motor Co., Ltd. is not responsible for any compensation for damage caused through failure to observe this warning.


### **Safety precautions**

The precautions described below are intended to ensure the safe and correct use of the product, and to prevent the customer and others from exposure to the risk of injury. Use the product only after carefully reading and fully understanding these instructions.

#### **Description of signs**

<b>AWARNING</b>	Handling the product without observing the instructions that accompany a "WARNING" symbol may result in serious injury or death.
	Handling the product without observing the instructions that accompany a "CAUTION" symbol may result in injury or property damage.
Note	The items under this heading contain important handling instructions that the user should observe to ensure the safe use of the product.

#### Description of graphic symbols



**WARNING** 

$\bigcirc$	<ul> <li>Do not use the product in explosive or corrosive environments, in the presence of flammable gases, in places subjected to splashing water, or near combustibles.</li> <li>Doing so may result in fire or injury.</li> <li>Do not forcibly bend, pull or pinch the lead wire or cable.</li> <li>Doing so may result in fire.</li> <li>Do not disassemble or modify the product.</li> <li>Doing so may result in injury.</li> </ul>
0	<ul> <li>Assign qualified personnel to the task of installing, wiring, operating/ controlling, inspecting and troubleshooting the product. Failure to do so may result in fire or injury.</li> <li>Take measures to keep the moving part in position if the product is used in vertical operations such as elevating equipment. Failure to do so may result in injury or damage to equipment.</li> <li>Install the product inside an enclosure. Failure to do so may result in injury.</li> <li>Connect the cables securely according to the wiring diagram. Failure to do so may result in fire.</li> <li>For the power supply, use a DC power supply with reinforced insulation on its primary and secondary sides. Failure to do so may result in electric shock.</li> </ul>

Thank you for purchasing an Oriental Motor product.

This Operating Manual describes product handling procedures and safety precautions. • Please read it thoroughly to ensure safe operation.

• Always keep the manual where it is readily available.

## 

$\bigcirc$	<ul> <li>Do not use the product beyond its specifications. Doing so may result in injury or damage to equipment.</li> <li>Keep your fingers and objects out of the openings in the product. Failure to do so may result in fire or injury.</li> <li>Do not touch the product during operation or immediately after stopping. The surface is hot, and this may cause a skin burn(s).</li> <li>Do not carry the motor by holding the motor output shaft, lead wire or cable. Doing so may result in injury.</li> <li>Keep the area around the product free of combustible materials. Failure to do so may result in fire or a skin burn(s).</li> <li>Leave nothing around the product that would obstruct ventilation. Failure to do so may result in damage to equipment.</li> <li>Do not touch the rotating part (output shaft) while operating the motor.</li> </ul>					
	Doing so may result in injury.					
	<ul> <li>Provide a cover over the rotating part (output shaft) of the motor. Failure to do so may result in injury.</li> <li>Use a motor and driver only in the specified combination. Failure to do so may result in fire.</li> <li>Provide an emergency stop device or emergency stop circuit external to the equipment so that the entire equipment will operate safely in the event of a system failure or malfunction. Failure to do so may result in injury.</li> <li>When an abnormal condition has occurred, immediately stop operation to turn off the driver power. Failure to do so may result in fire or injury.</li> <li>The motor surface temperature may exceed 70 °C (158 °F) even under normal operating conditions. If the operator is allowed to approach the motor in operation, affix a warning label shown in the figure on a conspicuous position. Failure to do so may result in a skin burn(s).</li> </ul>					

### **Precautions for use**

• When conducting the insulation resistance measurement or the dielectric strength test, be sure to separate the connection between the motor and the driver.

Conducting the insulation resistance measurement or dielectric strength test with the motor and driver connected may result in damage to the product.

• Do not apply a radial load and axial load in excess of the specified permissible limit

Continuing to operate the motor under a radial load or axial load exceeding the permissible value may cause damage the bearings (ball bearings) of the motor. Be sure to operate the motor within the specified permissible value of radial load and axial load.

#### Motor surface temperature

The surface temperature on the motor case may exceed 100 °C (212 °F) depending on operating conditions such as ambient temperature, operating speed, duty cycle and others. To prevent the bearings (ball bearings) of the motor from reaching its usable life quickly, use the motor in conditions where the motor surface temperature dose not exceed 100 °C (212 °F).

#### • Holding torque at standstill

The motor holding torque is reduced by the current cutback function of the driver at motor standstill. When selecting the motor, take account of the motor torque drop at the time of stopping.

### Checking the product

Verify that the items listed below are included. Report any missing or damaged items to the Oriental Motor sales office from which you purchased the product.

- Motor ......1 unit
- Connenction cable......1 pc. [0.6 m (2 ft.)] \*
- OPERATING MANUAL .....1 copy (this manual)

\* Included with the **PKP2□-L** 

### How to identify the product model

Check the model name of the motor against the model name shown on the nameplate.

**PKP2** 1 2 3 4 5 6 7 8 9

1	Motor frame size	1: 20 mm (0.79 in.)       5: 50 mm (1.97 in.)         2: 28 mm (1.10 in.)       6: 56.4 mm (2.22 in.)         3: 35 mm (1.38 in.)       9: 85 mm (3.35 in.)         4: 42 mm (1.65 in.)       9: 85 mm (3.35 in.)				
2	Motor length					
3	Motor type	Blank: Standard type M: High-resolution type P: High-torque type				
4	Number of lead wire	D: 4 pcs. U: 5 pcs. or 6 pcs.				
5	Motor winding specification	Representative example 05: Rated current 0.5 A/phase 28: Rated current 2.8 A/phase				
6	Shape	A: Single shaft B: Double shaft M: With electromagnetic brake				
7	Output shaft diameter	<b>A</b> : Imperial Blank: Metric				
8	Motor identification	<b>2</b> : Model A, Model B *1 Blank: Model B *2, Model C				
9	Connection cable	-L: Included with a connection cable Blank: Without connection cable				


\*1 Motor frame size 28 mm (1.10 in.)

\*2 Motor frame size 35 mm (1.38 in.), 42 mm (1.65 in.), 56.4 mm (2.22 in.)

### Names of parts


The pin numbers as well as the colors of lead wires are shown in the figures. The connection diagrams show our connection cable.

#### Motors of Model A (connector type)




#### Wiring connection diagram

Unipolar five lead wires type



• Bipolar four lead wires type \*




\* The pin No.3 is not used for the four lead wires type.


#### Applicable connector/lead wire


Туре	Model				
Connector housing	MDF97-5S-3.5C (HIROSE ELECTRIC CO., LTD.)				
Contact	MDF97-22SC (HIROSE ELECTRIC CO., LTD.)				
Designated crimping tool	HT801/MDF97-22S (HIROSE ELECTRIC CO., LTD.)				
Applicable lead wire	<ul> <li>AWG22 (0.3 mm<sup>2</sup>)</li> <li>Outer sheath diameter: ø1.2 to 1.5 mm (ø0.047 to 0.059 in.)</li> <li>Stripping length of wire insulation: 1.8 to 2.3 mm (0.071 to 0.091 in.)</li> </ul>				

#### • Motors of Model B (connector type)




### Wiring connection diagram










\* The pin Nos.2 and 5 are not used for the four lead wires type.

### Applicable connector/lead wire


Motor model	Туре	Model		
	Connector housing	51065-0600 (Molex Incorporated)		
	Contact	50212-8XXX (Molex Incorporated)		
	Designated crimping tool	63819-0500 (Molex Incorporated)		
PKP22	Applicable lead wire	<ul> <li>When the current value is less than 1 A/phase: AWG28 to 24 (0.08 to 0.2 mm<sup>2</sup>)</li> <li>When the current value is 1 A/phase or more: AWG26 to 24 (0.14 to 0.2 mm<sup>2</sup>)</li> <li>When the current value is 1.5 A/phase or more: AWG24 (0.2 mm<sup>2</sup>)</li> <li>Outer sheath diameter: ø0.8 to 1.4 mm (ø0.031 to 0.055 in.)</li> <li>Stripping length of wire insulation: 1.3 to 1.8 mm (0.051 to 0.071 in.)</li> </ul>		
	Connector housing	51103-0600 (Molex Incorporated)		
	Contact	50351-8XXX (Molex Incorporated)		
	Designated crimping tool	63811-8100 (Molex Incorporated)		
PKP23 PKP24	Applicable lead wire	<ul> <li>When the current value is less than 1.5 A/phase: AWG28 to 22 (0.08 to 0.3 mm<sup>2</sup>)</li> <li>When the current value is 1.5 A/phase or more AWG26 to 22 (0.14 to 0.3 mm<sup>2</sup>)</li> <li>When the current value is 2 A/phase or more: AWG24 to 22 (0.2 to 0.3 mm<sup>2</sup>)</li> <li>Outer sheath diameter: Ø1.15 to 1.8 mm (Ø0.045 to 0.071 in.)</li> <li>Stripping length of wire insulation: 2.3 to 2.8 mm (0.091 to 0.11 in.)</li> </ul>		

Motor model	Туре	Model		
	Connector housing	51067-0600 (Molex Incorporated)		
	Contact	50217-9XXX (Molex Incorporated)		
	Designated crimping tool	63811-8300 (Molex Incorporated)		
PKP26	Applicable lead wire	<ul> <li>AWG24 to 18 (0.2 to 0.75 mm<sup>2</sup>)</li> <li>Outer sheath diameter:</li> <li>Ø1.4 to 3 mm (Ø0.055 to 0.118 in.)</li> <li>Stripping length of wire insulation:</li> <li>3 to 3.5 mm (0.118 to 0.138 in.)</li> </ul>		

#### Motors of Model C (lead wire type)




### Wiring connection diagram



### Connection


#### • When inserting the connector

Hold the connector main body, and insert it in straight securely. Inserting the connector in an inclined state may result in damage to connector or a connection failure.



#### • When pulling out the connector

Pull out the connector in straight while releasing the lock part of the connector. Having the motor lead wires or pulling out the connector in a state of being locked may damage the connector.



Note

Secure the lead wires at the connection part of the connector to prevent the connector or terminals from receiving stress due to bending or selfweight of lead wires. Also, do not excessively bend the lead wires near the connection part of the connector. Applying stress on the motor lead wires may cause poor contact or disconnection, leading to malfunction or heat generation.

#### Connection with the drivers of Oriental Motor

Refer to the tables when connecting with the drivers of Oriental Motor. "Color" in the table represents the colors of lead wires of our connection cable.



The motors of the Model A and Model B are different in pin assignments. Wrong connection will not cause the motor to operate properly.

#### • Connection with the CVD driver

Driver	Model A		Mod	lel B	Model C
CN2 Pin No.	Pin No.	Color	Pin No.	Color	Color
1	4	Blue	1	Blue	Blue
2	5 Red		3	Red	Red
3	_		-	-	-
4	2	Green	6	Green	Green
5	1	Black	4	Black	Black

#### • Connection with the CMD driver

Driver	Model A		Мос	lel B	Model C
CN3 Pin No.	Pin No.	Color	Pin No.	Color	Color
1	4	Blue	1	Blue	Blue
2	3 White		2	White	White
3	5 Red		3	Red	Red
4	1	Black	4	Black	Black
5	_		5	Yellow	Yellow
6	2 Green		6	Green	Green

### Installation

#### Installation location


The motor is designed and manufactured to be incorporated in equipment. Install it in a well-ventilated location that provides easy access for inspection. The location must also satisfy the following conditions:

- Inside an enclosure that is installed indoors (provide vent holes)
- Operating ambient temperature –10 to +50 °C (+14 to +122 °F) (non-freezing)
- Operating ambient humidity 85 % or less (non-condensing)
- Area free of explosive atmosphere, toxic gas (such as sulfuric gas), or liquid
- Area not exposed to direct sun
- Area free of excessive amount of dust, iron particles or the like
- Area not subject to splashing water (rain, water droplets), oil (oil droplets) or other liquids
- · Area free of excessive salt
- Area not subject to continuous vibrations or excessive shocks
- Area free of excessive electromagnetic noise (from welders, power machinery, etc.)
- Area free of radioactive materials, magnetic fields or vacuum
  1,000 m (3,300 ft.) or lower above sea level


#### Installation method

Install the motor onto an appropriate flat metal plate having excellent vibration resistance and heat conductivity. When installing the motor, secure it with four screws (not included) through the four mounting holes provided. Do not leave a gap between the motor and metal plate.

#### • Installation method 1



### Installation method 2



Motor model	Nominal size	Tightening torque [N·m (lb-in)]	Effective depth of screw thread [mm (in.)]	Installation method
PKP21	M2 P0.4	0.25 (2.2)	2.5 (0.1)	
PKP22	M2.5 P0.45	0.5 (4.4)	2.5 (0.1)	1
PKP23 PKP24	M3 P0.5	1 (8.8)	4.5 (0.18)	
PKP25 PKP26	M4	2 (17.7)	_	2
PKP29	M5	3 (26.6)		

### Installing a load

When connecting a load to the motor, align the centers of the motor output shaft and load shaft. Be careful not to damage the output shaft or bearings when installing a coupling or pulley to the motor output shaft.

### Permissible radial load and permissible axial load

The radial load and axial load on the motor output shaft must be kept the permissible values listed in the tables.

#### Motors of Model A

		Permissible axial load				
Motor	Dist					
model	0 mm (0 in.)	5 mm (0.20 in.)	10 mm (0.39 in.)	15 mm (0.59 in.)	20 mm (0.79 in.)	[N (lb.)]
<b>PKP24</b> *1	35 (7.8)	44 (9.9)	58 (13)	85 (19.1)	-	15 (3.3)
<b>PKP24</b> *2	90 (20)	100 (22)	130 (29)	180 (40)	-	15 (5.5)
PKP25	61 (13.7)	73 (16.4)	90 (20)	110 (24)	-	20 (4.5)
<b>PKP26</b> *3	61 (13.7)	73 (16.4)	90 (20)	140 (31)	-	30 (6.7)
<b>PKP26</b> *2	90 (20)	100 (22)	130 (29)	180 (40)	270 (60)	50 (6.7)

\*1 Output shaft diameter ø5 mm (ø0.2 in.)

- \*2 Output shaft diameter ø8 mm (ø0.31 in.)
- \*3 Output shaft diameter ø6.35 mm (ø0.25 in.)

#### Motors of Model B and C

		Permissible						
Motor	Dist	Distance from the tip of motor output shaft						
model	0 mm (0 in.)	5 mm (0.20 in.)	10 mm (0.39 in.)	15 mm (0.59 in.)	20 mm (0.79 in.)	axial load [N (lb.)]		
PKP21	12 (2.7)	15 (3.3)	-	-	-	3 (0.67)		
PKP22	25 (5.6)	34 (7.6)	52 (11.7)	-	-	5 (1.12)		
PKP23 PKP24	20 (4.5)	25 (5.6)	34 (7.6)	52 (11.7)	-	10 (2.2)		
<b>PKP26</b> *1	49 (11)	60 (13.5)	79 (17.7)	110 (24)	-	20 (4.5)		
<b>PKP26</b> *2	61 (13.7)	73 (16.4)	90 (20)	110 (24)	160 (36)	20 (4.5)		
PKP29	260 (58)	290 (65)	340 (76)	390 (87)	480 (108)	60 (13.5)		

\*1 Output shaft diameter ø6.35 mm (ø0.25 in.)

\*2 Output shaft diameter ø8 mm (ø0.31 in.)

### Maintenance/inspection

#### Inspection

It is recommended that periodic inspections are conducted for the items listed below after each operation of the motor. If an abnormal condition is noted, discontinue any use and contact your nearest Oriental Motor sales office.

#### Inspection item

- Check if any of the screws having installed the motor is loose.
- Check if an unusual noise is generated from a bearing part (ball bearings) of the motor.
- Check if a damage or stress is applied on the motor lead wires.
- Check if the connection part with the connector or the driver is loose.
- Check if the motor output shaft and the load shaft are out of alignment.

#### Warranty

Check on the Oriental Motor Website or General Catalog for the product warranty.

#### Disposal

Dispose the product correctly in accordance with laws and regulations, or instructions of local governments.

### Specifications

Check on the Oriental Motor Website for the product specifications.

### **General specifications**

Degree of protection		IP20	
Operation environment	Ambient temperature	–10 to +50 °C (+14 to +122 °F) (non-freezing)	
	Humidity	85 % or less (non-condensing)	
	Altitude	Up to 1,000 m (3,300 ft.) above sea level	
	Surrounding atmosphere	No corrosive gas, dust, water or oil	
Storage environment, Shipping environment	Ambient temperature	-20 to +60 °C (-4 to +140 °F) (non-freezing)	
	Humidity	85 % or less (non-condensing)	
	Altitude	Up to 3,000 m (10,000 ft.) above sea level	
	Surrounding atmosphere	No corrosive gas, dust, water or oil	
Insulation resistance	100 $M\Omega$ or more when 500 VDC megger is applied between the case and motor windings.		
Dielectric strength	the winding an • PKP21, PKP2 • PKP25, PKP2	Sufficient to withstand the following conditions applied between the winding and the case for 1 minute: • PKP21, PKP22, PKP23, PKP24: 0.5 kVAC 50/60 Hz • PKP25, PKP26: 1.0 kVAC 50/60 Hz • PKP29: 1.5 kVAC 50/60 Hz	

### **Regulations and standards**

### RoHS Directive

The products do not contain the substances exceeding the restriction values of RoHS Directive (2011/65/EU).

- Unauthorized reproduction or copying of all or part of this manual is prohibited.
- Oriental Motor shall not be liable whatsoever for any problems relating to industrial property rights arising from use of any information, circuit, equipment or device provided or referenced in this manual.
- Characteristics, specifications and dimensions are subject to change without notice.
- While we make every effort to offer accurate information in the manual, we welcome your input. Should you find unclear descriptions, errors or omissions, please contact your nearest Oriental Motor sales office.
- **Orientalmotor** is a registered trademark or trademark of Oriental Motor Co., Ltd., in Japan and other countries.

© Copyright ORIENTAL MOTOR CO., LTD. 2012

Published in April 2021

Please contact your nearest Oriental Motor office for further information.

ORIENTAL MOTOR U.S.A. CORP Technical Support Tel:800-468-3982 8:30am EST to 5:00pm PST (M-F) www.orientalmotor.com

ORIENTAL MOTOR (EUROPA) GmbH Schiessstraße 44, 40549 Düsseldorf, Germany Technical Support Tel:00 800/22 55 66 22 www.orientalmotor.de ORIENTAL MOTOR (UK) LTD. Tel+44-1256347090 www.oriental-motor.co.uk ORIENTAL MOTOR (FRANCE) SARL Tel:+33-1 47 86 97 50 www.orientalmotor.fr ORIENTAL MOTOR ITALIA s.r.l. Tel:+39-02-93906347 www.orientalmotor.it ORIENTAL MOTOR CO., LTD. 4-8-1Higashiueno, Taito-ku, Tokyo 110-8536 Japan Tel:+81-3-6744-0361 www.orientalmotor.co.jp

ORIENTAL MOTOR ASIA PACIFIC PTE, LTD, Singapore Tel:1800-842-0280 www.orientalmotor.com.sg ORIENTAL MOTOR (MALAYSIA) SDN. BHD. Tel:1800-806-161 www.orientalmotor.com.my ORIENTAL MOTOR (THAILAND) CO., LTD. Tel:1800-888-881 www.orientalmotor.co.th ORIENTAL MOTOR (INDIA) PVT, LTD. Tel:1800-120-1995 (For English) 1800-121-4149 (For Hindi) www.orientalmotor.co.in TAIWAN ORIENTAL MOTOR CO., LTD. Tel:0800-060708 www.orientalmotor.com.tw SHANGHAI ORIENTAL MOTOR CO., LTD. Tel:400-820-6516 www.orientalmotor.com.cn INA ORIENTAL MOTOR CO., LTD. Korea Tel:080-777-2042 www.inaom.co.ki