

BLVシリーズ用

ドライバケーブル CC15D1、CC15D2

仕様とリード線の識別

お買い上げいただきありがとうございます。

はじめに

■ 製品について

このケーブルは、BLVシリーズ用です。その他の用途には使用しないでください。

ケーブル長さは2種類です。

品名	長さ
CC15D1	1 m
CC15D2	2 m

■ EMC指令に対して

この製品を使用した機器のEMC指令への適合性は、お客様自身で確認していただく必要があります。

■ RoHS指令

この製品は規制値を超える物質は含有していません。

仕様


コネクタ	種類	D-SUBコネクタ 15極 (JAE)
	ねじ締付トルク	0.3~0.39 N・m
ケーブル	外径	約9.8 mm
	シース材質	耐熱PVC
	定格電圧	AC300 V
	定格温度	105 °C
リード線	導体サイズ	AWG24 (0.22 mm ²)
	絶縁体外径	約1.5 mm
	絶縁体材質	耐熱PVC

リード線の識別

コネクタピンNo.	リード線		
	絶縁体色	ドット色	ドット数
1	橙	赤	1点
2	橙	黒	
3	灰	赤	
4	灰	黒	
5	白	赤	
6	白	黒	
7	黄	赤	
8	黄	黒	
9	桃	赤	
10	桃	黒	
11	橙	赤	2点
12	橙	黒	
13	灰	赤	
14	灰	黒	
15	白	赤	

● 絶縁体の表示

例:ピンNo.11のとき



重要

コネクタを外さないでください。ドライバが破損・誤動作する原因になります。

Orientalmotor は、日本その他の国におけるオリエンタルモーター株式会社の登録商標または商標です。

© Copyright ORIENTAL MOTOR CO., LTD. 2011

2025年5月制作

オリエンタルモーター株式会社
お客様ご相談センター

TEL 0120-925-410

BLV Series

Driver cable CC15D1, CC15D2

Specification and Check points of core wire

Thank you for purchasing an Oriental Motor product.

Introduction

■ Overview of the product

The product described in this manual has been designed and manufactured for use as **BLV** series must not be used for any other purpose.
Two types of cable length are available.

Model	Length
CC15D1	1 m (3.3 ft.)
CC15D2	2 m (6.6 ft.)

■ For EMC Directive

Users should confirm compliance of their equipment using this cable with EMC Directive themselves.

■ RoHS Directive

This product does not contain the substances exceeding the restriction values.


Specification

Connector	Type	D-sub connector 15 circuit (JAE)
	Tightening torque of screw	0.3 to 0.39 N·m
Cable	Outside diameter	About 9.8 mm (0.39 in.)
	Sheath material	Heat resistance PVC
	Rated voltage	300 VAC
	Rated temperature	105 °C (221 °F)
Lead wire	Conductor size	AWG24 (0.22 mm ²)
	Insulation outside diameter	About 1.5 mm (0.06 in.)
	Insulation material	Heat resistance PVC

Check points of core wire

Connector pin No.	Leadwire side		
	Insulation color	Dots color	No. of dots
1	Orange	Red	1
2	Orange	Black	
3	Gray	Red	
4	Gray	Black	
5	White	Red	
6	White	Black	
7	Yellow	Red	
8	Yellow	Black	
9	Pink	Red	2
10	Pink	Black	
11	Orange	Red	
12	Orange	Black	
13	Gray	Red	
14	Gray	Black	
15	White	Red	

● e.g.Indication of insulation for circuit No.11



Do not disassemble the connector. Doing so may result in damage or malfunction of the driver.

Orientalmotor is a registered trademark or trademark of Oriental Motor Co., Ltd., in Japan and other countries.

© Copyright ORIENTAL MOTOR CO., LTD. 2011

Published in May 2025

• Please contact your nearest Oriental Motor office for further information.

ORIENTAL MOTOR U.S.A. CORP.
Technical Support Tel:800-468-3982
8:30am EST to 5:00pm PST (M-F)

ORIENTAL MOTOR (EUROPA) GmbH
Schiessstraße 44, 40549 Düsseldorf, Germany
Technical Support Tel:00 800/22 55 66 22

ORIENTAL MOTOR (UK) LTD.
Blythe Valley Business Park,
Central Blvd Blythe Valley Park,
Solihull B90 8AG, United Kingdom
Tel:+44-1926-671 220

ORIENTAL MOTOR (FRANCE) SARL
Tel:+33-1 47 86 97 50

ORIENTAL MOTOR ITALIA s.r.l.
Tel:+39-02-93906347

ORIENTAL MOTOR CO., LTD.
4-8-1 Higashiueno, Taito-ku, Tokyo 110-8536
Japan
Tel:+81-3-6744-0361
www.orientalmotor.co.jp/ja

ORIENTAL MOTOR ASIA PACIFIC PTE. LTD.
Singapore
Tel:1800-842-0280

ORIENTAL MOTOR (MALAYSIA) SDN. BHD.
Tel:1800-806-161

ORIENTAL MOTOR (THAILAND) CO., LTD.
Tel:1800-888-881

ORIENTAL MOTOR (INDIA) PVT. LTD.
Tel:1800-120-1995 (For English)
1800-121-4149 (For Hindi)

TAIWAN ORIENTAL MOTOR CO., LTD.
Tel:0800-060708

SHANGHAI ORIENTAL MOTOR CO., LTD.
Tel:400-820-6516

INA ORIENTAL MOTOR CO., LTD.
Korea
Tel:080-777-2042