
Oriental motor

> NEW 3-Finger Type 2-Finger Type



Delicate grip.






Compact and Lightweight Gripper

● Size: 80.5 mm×36 mm×42.5 mm

Mass: 200 g

The EH3-AZAKH is shown



Differentiating "Light and Gentle" from "Firm and Secure"


Minimum grip force 2 N*1. Maximum grip force 25 N*2.

Current control allows the grip force to be minutely changed and regulated.

Appropriately grips loads either gently or firmly, whether delicate or slippery.

*1 EH3-AZAKH (reference value)


*2 EH4-AZAKH



The AZ Series Provides a Delicate Grip


A delicate grip is achieved by fine-tuning the grip force in 1% operating current increments and implementing a slow approach to the load.

Please prepare attachments (hooks) separately.



Useful as a Network Compatible End Effector

EtherNet/IP, EtherCAT, and PROFINET compatible drivers are available. It is optimal as an end effector for equipment or robots controlled over a single network.




 Installation Flanges for Robots are Available for Installation on Commercially Available Industrial Robots (Collaborative robots).
 Flanges on the robot side conform to IS09409-1 (JIS B 8436).
 For product details on product, refer to page 22.



Main Compatible Manufacturers Yaskawa Electric Corporation Seiko Epson Corporation

Driven by an **QSTEP AZ** Series Motor

- Built-In battery-free absolute sensor, for constant monitoring of motor position information without an external sensor
- High reliability with closed loop control
- High efficiency technology reduces motor heat generation and saves energy



Comparison of 2-Finger and 3-Finger Types

Туре	2-Finger*1	3-Finger
	Square	Cylinders, complex shapes, spheres
Suitable for Gripping Load Shape		
Moving Range	25 mm	When Open: P.C.D.\phi30.9 mm When Cosed: P.C.D.\phi7 mm Opening Width: \phi23.9 mm
Max. Gripping Force [N]	25	50
Permissible Load [N] (Permissible axial load [N]*2)	5	15
Mass [kg]	0.38	0.38 (with installation cover) / 0.28 (without installation cover)

 $^{^{\}star}1$ The values correspond to the specifications for Model 4

^{*2} For 3-finger type

Basic Performance of the EH Series of Electric Gripper

Compact and Lightweight

Minimizes the Burden on the Robot

2-Finger/3-Finger


•EH3-AZAKH




•EH4-AZAKH



 Reduces the Burden on Each Articulation, Decreasing the Overall Size and Cost of the Robot




•EH4T-AZAKH



•EH4T-AZAK



 No Installation Cover Allows for Increased Design Freedom and Weight Reduction




Fine-tuned Grip Force Control

Real Grip, Like that of a Human Hand

2-Finger/3-Finger

•Grip Force and Running Current (Reference values)



 Grips Gently without Causing . Damage



Two-Stage Gripping without Dropping the Load



■Transitions in Grip Force <Image>




Grip Force Time

Long Stroke

Compatible with Loads of Different Configurations

2-Finger


•EH3-AZAKH



•EH4-AZAKH



Continuous Operation without Replacing Attachments, Even for Loads with Uneven Configurations



Applications Using the Electric Gripper's "Delicate Grip"

Grip

Reliably Grip Loads that may Easily Deform or Break.


2-Finger/3-Finger

Easily set the grip force, grip time, and speed according to the object being gripped.

Safely and reliably grip objects that may easily break, such as glass, and objects that easily deform, such as plastic or springs.

Quick Approach, Slow Grip

The motor approaches the load at high speed. The motor decelerates just before hitting the surface at low speed.





2 Adjust

The Direction and Position of the Load can be Coordinated.

2-Finger/3-Finger

The minimum travel distance of the fingers is 0.02 mm. The direction and position of components can be coordinated by gripping them according to their size.





3 **Measure**


The Size of the Load can be Verified without an External Sensor.

2-Finger

Host PLC

The Size and Presence of a Load are Determined within the Operational Range of the Fingers


The operational range of the pincer is confirmed by the output signal (TLC output, AREA output) from the driver, allowing the size and presence of a load to be determined.




①② Determine the size of the load



The position of the attachment when the load is



② NG (out of tolerance)



3 NG (no load present)

3 Detect the presence of a load

Determine whether or not a load is




AREA output: This signal is output when the motor is in a set area.

TLC output: This signal is output during push-motion operation when the output torque reaches a set torque limit value.

gripped is confirmed, allowing for sorting by size. Monitor the Gripper Position to Measure Size

The Coordinates Information Monitoring Function in the driver sends data from the gripper to the host PLC, allowing the size of the load to be measured.

gripped.



Measure the load size



 \star Coordinates information monitoring function: This function sends position data to the host system.

Please prepare attachments (hooks) separately.

Register the Gripper's Operation Program in the Driver to Distribute the Load on the Host System

Applicable Products: Built-in controller type drivers and network compatible drivers (excluding EtherCAT)

The **EH** Series can register the state of sensors and other external input signals, as well as its own output signals, in the driver with a simple sequence program while in use.

In simple applications, operation is possible with only a START/STOP command.

Real-time Monitoring of the State of the Motor

Actuators equipped with an α Step AZ Series, including the EH Series, are able to constantly monitor the state of a motor over a network.

Motor Temperature Monitor


Real-time temperature monitoring is possible, even if the robot is inside a case, etc.



For monitoring details, refer to the AZ Series operating manual.


Cumulative Load Monitor

Besides an instantaneous load factor monitor, the load factor in the motor's operating pattern can also be obtained via area and detected as a value. This allows long-term changes in load due to age deterioration and other factors to be understood.



ODO/TRIP Monitor

The cumulative number of rotations can be monitored, like with a car's gauges. An information signal can be output when a set threshold is reached. This is useful for maintenance and other applications.




◆ Dedicated Support Software MEXEO2 (Free download)

Operating data editing, parameter setting, and other such basic settings can be easily made on a computer. Simple sequence programs can also be created.




to operate even without a background in electrical design!





Teaching is also possible from a computer



Check the signal's input status
Also equipped with waveform monitor

Product Line of **EH** Series

Electric Grippers

EH3-AZAKH



EH4-AZAKH



EH4T-AZAKH



EH4T-AZAK



Drivers DC Input

Built-in Controller Type

Set the positioning data in the driver (256 points). FA network control is possible with a network converter (sold separately).



Pulse Input Type with RS-485 Communication

The motor's position, speed, torque, alarms, and temperature can be monitored via RS-485 communication.



Pulse Input Type

The motor is controlled from a positioning module (pulse generator).



Network Compatible

The driver can be directly controlled from a host control device over an FA network.



EtherNet/IP EtherCAT.

mini Driver

Modbus (RTU) compatible



◆ For Delicate Operations, We Recommend the EH Series Over a Pneumatic Gripper!

Adjust the Grip Force in 1 % Increments

Adjustment with a pneumatic gripper's regulator (pressure reducing valve) is unnecessary. The grip force can be easily and finely adjusted with digital settings.

Adjust the Traveling Amount in **0.02** mm Increments

This gripper utilizes the height of the stepper motor's positioning accuracy. This allows loads of various configurations to be approached. Adjust the Speed in 0.02 mm/s Increments

Adjustment with a pneumatic gripper's speed controller (speed control valve) is unnecessary. Speed regulation is easy as a result of control with a stepper motor, making gripping possible at low speeds.

Position
Monitoring with
an Absolute
Sensor

Feedback of detailed position information allows for not only grip and transportation, but also the size of the load to be determined.

■System Configuration

• Combination of Electric Gripper and Built-in Controller Type Driver, or Pulse Input Type Driver with RS-485 Communication An example of a configuration using I/O control or RS-485 communication is shown below.

Electric gripper, driver, and a connection cable/flexible connection cable are ordered separately.

• For a pulse input type driver system configuration, please see the Oriental Motor website.

- Required for operationOptional accessory
- Oriver Electric Gripper Connection Cable → Page 13 For Motor/Encoder Extension cables used to lengthen connection cables and flexible cables used on moving parts are available in a variety of types and lengths. ODC Power Supply Cable → Website DC Power Supply (Main power supply) Support Software MEXEO2 Not supplied. USB Cable ●The **MEXEO2** Data Setting Software can be downloaded from Oriental Motor Website. To connect to the host controller, three methods are available; I/O control, control via FA network O Cable for I/O Signals → Website I/O Control Network Host Controller Converter ○ RS-485 Communication Cable → Website → Website Control via FA Network Cable for FLEX Communication → Website Control via Modbus

●Example of System Configuration


			Cables		
	Driver		Connection Cable (1 m)	Cable for I/O Signals	
1		1	Collifection Cable (1 iii)	Connector Type (1 m)	
—	AZD-KD	—	CC010VZ2F2	CC16D010B-1	
	\$485.00		\$39.00	\$28.00	
	O		O	0	
	+	+ AZD-KD	+ AZD-KD +	Driver Connection Cable (1 m) + AZD-KD + CC010VZ2F2	

[•] The system configuration shown above is an example. Other combinations are also available.
Note

The motor cable and encoder cable from the motor cannot be connected directly to the driver. When connecting to a driver, use a connection cable

Combination of Electric Gripper and Network Compatible Driver

An example of a configuration using I/O control with an EtherNet/IP-compatible driver or EtherNet/IP is shown below. Electric gripper, driver, and a connection cable/flexible connection cable are ordered separately.



●Example of System Configuration

			Cables		
Electric Gripper	,	Driver	,	Connection Cable (1 m)	Cable for I/O Signals General-Purpose Type (1 m)
EH4-AZAKH	+	AZD-KEP	+	CC010VZ2F2	CC16D010B-1
\$835.00		\$557.00		\$39.00	\$28.00
O		•		O	0

[•] The system configuration shown above is an example. Other combinations are also available.
Note

The motor cable and encoder cable from the motor cannot be connected directly to the driver. When connecting to a driver, use a connection cable.

■Product Number

Electric Gripper

EH 4 T - AZ A K H

① ② ③ ④ ⑤ ⑥ ⑦

Driver

AZD - K D ① ② ③

Connection Cable/Flexible Connection Cable

CC 050 V Z 2 F 2

1	Series Name	EH: EH Series
2	Product Number	3 : 36 mm (W)×36 mm (H) (Finger side) 4 : 46 mm (W)×46 mm (H) (Finger side)
3	Finger Type	None: 2-Finger Type T : 3-Finger Type
4	Motor	AZ: AZ Series
(5)	Additional Function	A: Without Additional Function
6	Motor Type	K: DC Power Supply Input
7	Configuration	H: With installation cover None: No installation cover

1	Driver Type	AZD: AZ Series Driver
2	Power Supply Input	K : 24 VDC
3	Product Line	D: Built-in Controller Type X: Pulse Input Type with RS-485 Communication Blank: Pulse Input Type EP: EtherNet/IP Compatible ED: EtherCAT Drive Profile Compatible PN: PROFINET Compatible

1		CC: Cable
2	Length	005: 0.5 m 010: 1 m 015: 1.5 m 020: 2 m 025: 2.5 m 030: 3 m 040: 4 m 050: 5 m 070: 7 m 100: 10 m 150: 15 m 200: 20 m
3	Reference Number	
4	Applicable Model	Z: AZ Series
(5)	Reference Number	2: Frame Size 20 mm, 28 mm
6	Cable Type	F: Connection Cable R: Flexible Connection Cable
7	Cable Specifications	2: DC Power Supply Input

■Product Line

Electric Gripper







Product Name	List Price
EH3-AZAKH EH4-AZAKH	\$835.00

Product Name	List Price
EH4T-AZAKH	\$835.00

Product Name	List Price
EH4T-AZAK	\$789.00

Driver

 \Diamond Built-in Controller Type



◇Pulse Input Type
with RS-485 Communication




◇Pulse Input Type



Product Name	List Price
AZD-KD	\$485.00

Product Name	List Price
AZD-KX	\$485.00









|--|



Product Name	List Price
AZD-KEP	\$557.00

Product Name	List Price
AZD-KED	\$557.00

Product Name	List Price
AZD-KPN	\$557.00

Connection Cable/Flexible Connection Cable

Use a flexible connection cable if the cable will be bent.

♦ For Motor/Encoder



	Product Line	Length (m)	Product Name	List Price	Product Line	Length (m)	Product Name	List Price	
		0.5	CC005VZ2F2	\$39.00			0.5	CC005VZ2R2	\$92.00
		1	CC010VZ2F2	\$39.00		1	CC010VZ2R2	\$92.00	
		1.5	CC015VZ2F2	\$47.00		1.5	CC015VZ2R2	\$99.00	
		2	CC020VZ2F2	\$55.00		2	CC020VZ2R2	\$109.00	
		2.5	CC025VZ2F2	\$61.00		2.5	CC025VZ2R2	\$114.00	
	Connection Cable	3	CC030VZ2F2	\$68.00	Flexible Connection Cable	3	CC030VZ2R2	\$121.00	
		4	CC040VZ2F2	\$105.00		4	CC040VZ2R2	\$138.00	
		5	CC050VZ2F2	\$120.00		5	CC050VZ2R2	\$155.00	
		7	CC070VZ2F2	\$149.00		7	CC070VZ2R2	\$198.00	
		10	CC100VZ2F2	\$194.00			10	CC100VZ2R2	\$259.00
		15	CC150VZ2F2	\$268.00		15	CC150VZ2R2	\$365.00	
		20	CC200VZ2F2	\$340.00		20	CC200VZ2R2	\$469.00	
_	·		·			-	·	-	

Included Items

Electric Gripper

Operating Manual: 1 Copy

Driver

Included Items Type	Connector
Built-in Controller Type Pulse Input Type with RS-485 Communication Pulse Input Type	CN1 Connector (1 pc.) CN4 Connector (1 pc.)
EtherNet/IP Compatible EtherCAT Drive Profile Compatible PROFINET Compatible	CN1 Connector (1 pc.) CN4 Connector (1 pc.) CN7 Connector (1 pc.)


Connection Cable/Flexible Connection Cable

Included Items Type	Operating Manual
Connection Cable	_
Flexible Connection Cable	1 Set

Explanation of Terminology in Specifications Table

Туре	2-Finger	3-Finger	
Maximum Gripping Force	This is the maximum force used to grip the load.		
Repetitive Positioning	A value indicating the degree of error that generates when positioning is		
Accuracy	performed repeatedly to the same position in the same direction	-	
Accuracy	(measured at a constant temperature and under a constant load).		
Backlash	This is the play of the finger when the motor shaft is fixed.	-	
Stroke	This is the maximum distance that the finger can open or close.	-	
Gripping Diameter	-	This is the diameter of the load that can be gripped.	
Gear Ratio	-	This is the ratio of the rotation speed between the input speed from the motor and rotational speed of the finger.	
Maximum Speed	This is the maximum speed that the fingers can open or close.		
Maximum Acceleration	This is the maximum acceleration at which the fingers can open or close.	-	
Push-Motion Speed	This is the operating speed for push-motion operation (gripping operation)		
Minimum Traveling Amount	This is the factory setting for the traveling amount per 1 pulse.	-	
Permissible Load	This is the permissible external force.	-	
Static Permissible Moment	This is the permissible moment during gripping operation.	-	
Permissible Axial Load	_	This is the permissible load that can be applied in the finger's axial	
- CITIIOSIDIO ANIAI LUAU		direction.	
Permissible Radial Load	-	This is the permissible load that can be applied perpendicular to the finger.	

Load Moment Formula



 $\varDelta\,M_{\text{P}}\!\!:$ Load moment in the pitching direction (N·m)


 $\varDelta \, \text{My:}$ Load moment in the yawing direction (N·m)


 Δ M_R: Load moment in the rolling direction (N·m)

 $M_{\textrm{P}}\text{:}$ Permissible moment in the pitching direction (N·m)


 $M_{\mbox{\scriptsize Y}}\!:$ Permissible moment in the yawing direction (N·m)


 $M_{\mbox{\scriptsize R}}\!\!:$ Permissible moment in the rolling direction (N·m)





Correlation between radial load and gripping position (reference value)





Specifications

2-Finger Type

Actuator Product Name		EH3-AZAKH	EH4-AZAKH
Motor (AZ Series)		AZM14	AZM24
Maximum Grip Force [N]		7	25
Repetitive Positioning Accuracy [mm]	each side	±0.02	±0.02
Backlash [mm]	each side	0.2	0.1
Stroke [mm]	both sides	15	25
Sticke [iiiii]	each side	7.5	12.5
Max. Speed [mm/s]	both sides	156	156
wax. Speed [IIIII/S]	each side	78	78
Maximum Acceleration [m/s ²]	both sides	20	20
Maximum Acceleration [m/s]	each side	10	10
Push Speed [mm/s]	both sides	20	20
rusii speeu [iiiii/s]	each side	10	10
both sides		0.02	0.02
Minimum Travel Amount [mm]	each side	0.01	0.01
Permissible Load [N]		2	5
Static Permissible Moment [N·m]*		Mp: 0.7	Mp: 1.2
		My: 0.2	My: 0.12
	M _R : 0.2	M _R : 0.4	

*The static permissible moment at the finger end. The load, attachment mass, grip force (including impact load), etc. should be considered when using.

| Note |

The actual load mass that can be transported varies greatly depending on the attachment, the friction coefficient of the load, and the acceleration. Use it with a sufficient margin, with an upper limit of 1/10 of the grip force.

3-Finger Type

Actuator Product Name	With Installation Cover	EH4T-AZAKH
Actuator Product Name	Without Installation Cover	EH4T-AZAK
Equipped Motor (AZ Serie	es)	AZM24
Gear Ratio		5
Maximum Gripping Force [N]	50
Gripping Diameter	Grips the outside diameter of the object to be gripped	φ2~ φ24
[mm]* ¹ * ²	Grips the inner diameter of the object to be gripped	ф14∼ф36
Max. Speed [r/min]*3		1200
Push-Motion Speed [r/min]*3		12
Permissible Axial Load [N]		15
Permissible Radial Load [N]*4		23

- *1 This value takes into account a clearance of approximately 0.5 mm (min. value) relative to the diameter (D) of the object to be gripped.
- $\mbox{\ensuremath{\$}}2$ When the attachment diameter (d) is $\varphi 6$ mm.
- $\bigstar 3$ This is the finger speed.
- *4 This is the value 10 mm from the attachment installation surface. This is the sum of the mass of the load and the attachment and the gripping force (includes shock load).

 Note
- The actual mass of the load that can be transported varies greatly depending on the attachment, friction coefficient of the load, acceleration, and other factors.
- Use 1/10 of the gripping force as the upper limit and allow sufficient margin.
- Depending on the design of the object to be gripped and the attachment, the gripping force may exceed the maximum gripping force.
- If the product is used under these conditions, it may be damaged.
- If the maximum gripping force is exceeded, adjust the running current to reduce the actual gripping force to less than the maximum gripping force.

Relationship between Push Force (Grip Force) and Current


The gripping movement of the electric gripper depends on the push-motion operation.

The push force (grip force) is set by the operating current of the motor.


Actual Push Force (Grip force)

The push force (grip force) and current values are shown below as a reference.

Check it on the actual assembled equipment.




EH3-AZAKH



- Set the grip force during push-motion operation to 7 N or less.
- Set the operation speed during push-motion operation to 10 mm/s or less (single side).

ΕΗ4-ΔΖΔΚΗ



- Set the grip force during push-motion operation to 25 N or less.
- Set the operation speed during push-motion operation to 10 mm/s or less (single side).

Relationship between Push Force (Gripping Force) and Current


The gripping movement of the electric gripper is performed with push-motion operation.


The push force (gripping force) is set by the operating current.

3-Finger Type Push Force (Gripping force) Reference Values

Reference values for the outer diameter (or inner diameter) of the gripped object, attachment diameter and gripping force at each operating current are shown below. Check the actual push force (gripping force) using the equipment.


The gripping force of the 3-finger type varies depending on the size of the load to be gripped.





- Front View
- F: Gripping force [N]
- d: Attachment diameter [mm]
- $D\!\!:$ Outer diameter (or inner diameter) of gripped object [mm]

• Relationship between Gripped Object, Attachment Diameter and Push Force (Gripping force) [Reference Value]





- \cdot When gripping the outer diameter of the gripped object. D+d: Pitch circle diameter [mm]
- \cdot When gripping the inner diameter of the gripped object. D-d: Pitch circle diameter [mm]

♦ Gripping Force and Gripping Diameter Formulas


The gripping force can be calculated using the formula shown below.

Because the gripping force varies with the diameter of the object to be gripped, adjust the gripping force according to the size, mass, and strength of the object.





- F: Gripping force [N]
- d: Attachment diameter [mm]
- D: Outer diameter (or inner diameter) of the object to be gripped [mm]



Finger operation

- R: Attachment's rotation radius [mm] (=6.4)
- θ : Finger's rotation angle[°]

• Gripping force formula

• Gripping diameter formula

- When gripping the outer diameter of the object to be gripped $D=2\times\sqrt{(9.05+r\times\cos\theta)^2+(r\times\sin\theta)^2}-d$
- When gripping the inner diameter of the object to be gripped $D=2\times\sqrt{(9.05+r\times\cos\theta)^2+(r\times\sin\theta)^2}+d$

■Driver Specifications

	Product Name		AZD-KD, AZD-KX, AZD-K	AZD-KEP, AZD-KED, AZD-KPN	
	Input Voltage	EH3	24 VDC±5%		
Main Power	iliput voltage	EH4			
Supply	Input Current	EH3	0.5 A 0.4 A		
	input Guirent	EH4	1.6 A	1.6 A	
Control Power	Input Voltage		_	24 VDC±5%	
Supply	Input Current		_	0.15 A	

■General Specifications

	Electric Gripper		Driver	
Thermal Class		130 (B) —		
Insulation Resistance		$ \begin{array}{lll} 100 \ M\Omega \ \text{or more when a 500 VDC megger is applied between the} \\ \text{following places:} \\ \cdot \ \text{Between the case and motor windings} \end{array} \begin{array}{ll} 100 \ M\Omega \ \text{or more when a 500 VDC megger is applied between the} \\ \text{following places:} \\ \cdot \ \text{Between the protective earth terminal and the power supply to} \end{array} $		
Dielectric Strength		Sufficient to withstand the following for 1 minute: Between the case and motor windings: 0.5 kVAC, 50 Hz or 60 Hz		
On exeting For insurant	Ambient Temperature	0 to +40°C (Non-freezing)*	0 to +50°C (Non-freezing)	
Operating Environment (In operation)	Ambient Humidity	85% or less (Non-condensing)		
	Atmosphere	Use in an area without corrosive gases and dust. The product should not be exposed to water, oil or other liquids.		
Degree of Protection		_ IP10		

^{*} Based on Oriental Motor's internal measurement conditions


Note

Disconnect the motor and driver when taking an insulation resistance measurement or performing a dielectric voltage withstand test. Also, do not perform these tests on the absolute sensor part of the motor.


■Travel Direction

The default factory setting for direction of travel is as follows:

2-Finger Type




3-Finger Type



Dimensions (Unit: mm)

2-Finger Type With Installation Cover



The _____ shaded areas are moving parts.

2D & 3D CAD 2D CAD

Mass kg


Product Name

EH4-AZAKH	0.38	D7903	
3 ^{+0.018} 3 Deep	Detail of "A"	46 (36) 25±02 7-7	(48.5) 23.5, 25 4×M4 6 Deep 25±0.2 ф10 H7(+0.015)3 Deep
37.5 14.5 14.5 14.5 27.2 14.5 27.2	×M4 6 Deep (Same 3 + 0.018 3 Deep (Same 2 + 0.018 3 Deep 2 + 0.018 3 Deep (Same 2 + 0.018 3 Deep (Same 2 + 0.018 3 Deep 2 + 0.018 3 Deep (Same 2 + 0.018 3 Deep 2 + 0.018 3 Deep (Same 2 + 0.018 3 Deep 2 + 0.018	anical Limit Position	.5 6.5 Home

[●] The _____ shaded areas are moving parts.


3-Finger Type

With Mounting Cover			2D & 3D CAD
	Product Name	Mass kg	2D CAD
	EU/IT.A7AVU	0.38	D7022H



♦ Without	Mounting	Cover
<> vvitriout	Mountina	Cover

Without Mounting Cover		2D & 3D CAD
Product Name	Mass kg	2D CAD
FUAT A 7 A V	0.00	D7022



The shaded areas are moving parts.

Peripheral Equipment

Installation Flange for Robots

This flange can be installed on commercially available industrial robots.

It helps reduce man-hours for jig design and production.

Installation flanges on the robot side conform to ISO9409-1 (JIS B 8436).

They can be installed on each robot manufacturer's SCARA robots and vertical articulated robots.





End Effector Side

Robot Side

Combination Example

Product Line

Product Name	List Price	Applicable ISO Standards on Robot Side	Applicable Product
P3F1	\$184.00	Conforms to ISO 9409-1-31.5-4-M5	EH3
P3F2		Comornis to 130 9409-1-31.5-4-W5	EH4
P5F1		Conforms to ISO 9409-1-50-4-M6	EH3
P5F2			EH4


Included Items

Positioning Pins, Hexagonal Socket Head Screws*, Operating Manual *Bolts for connecting the industrial robot and the installation flange for robot are not supplied.


Dimensions (Unit: mm) 2D & 3D CAD

Product Name	Mass kg	2D CAD
P3F1		D7919
P3F2	0.13	D7920
P5F1		D7921
P5F2		D7922


◇P3F1




◇P3F2



⇔P5F1



◇P5F2



Examples of Industrial Robots that Can be Combined

Corporation

Example of Compatible Product: -MOTOMAN-HC Series



Example of Compatible Product:

-T Series

-VT



Product Variation with the AZ Series

Controllability is consolidated across all product groups that contain the AZ Series.



Battery-Free Absolute Sensor

AZ Series



Hollow Rotary Actuator

DGII Series



Compact Linear Actuator

DRS Series

Simplify Setup & Control



Electric Linear Slides

EZS Series



Electric Cylinders

EAC Series



Rack & Pinion

L Series

Specifications are subject to change without notice. This catalog was published in June 2023.

ORIENTAL MOTOR U.S.A. CORP.

Western Sales and Customer Service Center Tel: (310) 715-3301 Fax: (310) 225-2594

Los Angeles Tel: (310) 715-3301

San Jose

Tel: (408) 392-9735

Midwest Sales and **Customer Service Center**

Tel: (847) 871-5900 Fax: (847) 472-2623

Chicago

Tel: (847) 871-5900

Toronto

Tel: (905) 502-5333

Eastern Sales and Customer Service Center Tel: (781) 848-2426 Fax: (781) 848-2617

Tel: (781) 848-2426

New York

Tel: (973) 359-1100

Technical Support Tel: (800) 468-3982 / 8:30 A.M. to 5:00 P.M., P.S.T. (M-F) 7:30 A.M. to 5:00 P.M., C.S.T. (M-F)

E-mail: techsupport@orientalmotor.com

Obtain Specifications, Online Training and Purchase Products at: www.orientalmotor.com