
CMK Series

●Additional Information●
Technical reference → Page F-1


The **CMK** Series is a motor and driver package consisting of a 2-phase stepping motor and 24 VDC input microstep driver, allowing for a reduction in the size of your equipment and in vibration.



Features

Achieving Low Vibration and Noise in a Microstep Drive

The newly designed DC board-level microstepping driver is compact and lightweight. The 2-phase stepping motor's basic step angle (1.8°/step) is divided by a maximum of 16 resolutions (0.1125°/step) without the use of a reduction mechanism or other mechanical elements, which contributes to the reduction in noise and vibration of your equipment.




Full Range of Driver Functions

- Five preset step angles
- Operating current can easily be set with a digital switch
- 1-pulse/2-pulse input mode switching
- Power LED
- Connector with lock (by MOLEX)

Microsteps/Step	Resolution	Step Angle	
1	200	1.8°	
2	400	0.9°	
4	800	0.45°	
8	1600	0.225°	
16	3200	0.1125°	

(At basic step angle 1.8°/step)

Comparison of Noise Characteristics










Vertical Installation

One of the Smallest Microstep Drivers in the Industry

The **CMK** Series driver is one of the smallest, lightest microstep driver in the industry. The driver is 62% lighter and has 41% less install area (based on horizontal installation) compared to our conventional model. This product contributes to downsizing of your equipment.

Mass: 130 g (0.29 lb.)







65 mm (2.56 in.)

Comparison with a conventional driver

♦ Install area: 41 % less (based on horizontal installation)

♦ Volume: 41 % less

The conventional driver includes a 5 mm (0.2 in.) spacer for installation.]

Conventional Model (CSD2120-T)


New Product (CMD21□□P)

Mass: 50 g (0.11 lb.)


High-Torque Type

The high-torque type adopts new technology and design. The motor produces approximately 50% higher torque than a conventional stepping motor of the same size.

Comparison of Speed – Torque Characteristics



Providing torque equivalent to a motor of the next larger frame size, the high-torque type allows for a reduction in the size of your equipment.




The high-torque type is connected using a connector – a connection method everyone is familiar with.

- Desired cable length and type can be selected.
- Maintenance becomes easy.
- Motor lead wire/connector assembly [0.6 m (2 ft.)] is included with motor and driver package.


High-Resolution Type

The basic step angle is 0.9°, which is half that of the standard type. 400 steps per rotation is possible. This motor achieves high resolution, low vibration and improved stopping accuracy.



The small basic step angle allows the torque to increase sharply while minimizing the negative effect of friction load.

Comparison of Angle - Torque Characteristics



• (RoHS) RoHS-Compliant

The CMK Series conforms to the RoHS Directive that prohibits the use of six chemical substances including lead and cadmium. ■ Details of RoHS Directive → Page G-38


Wide Variety

The **CMK** Series motor and driver package comes in five frame sizes of 28 to 60 mm (1.10 to 2.36 in.) as well as four motor types.

Туре	Features	□28 mm (□1.10 in.)	□35 mm (□1.38 in.)	□42 mm (□1.65 in.)	□50 mm (□1.97 in.)	□56.4/60 mm (□2.22/2.36 in.)	Driver
High-Torque Type	A high-torque motor has higher torque of approx. 1.5 times compared with the conventional standard type motor.	7	3	5			
High-Resolution Type	A high-resolution type offers higher positioning accuracy with the basic step angle set to 0.9°/step, which is just half the basic step angle of the standard type motor.						
Standard Type	The basic model offering a good balance of torque and low vibration/noise characteristics.				0		
SH Geared Type	These geared types are effective for inertia reduction, increasing torque, higher resolution and suppressing vibration. Six gear ratios are available.						

System Configuration

An example of a system configuration with the **\$G8030J** controller.



No.	Product Name	Overview	Page
1	Controller	This controller outputs pulse commands that determine the rotation amount and rotating speed.	C-269
2	Motor Mounting Brackets	Dedicated mounting bracket for the motor.	C-312
3	Flexible Couplings	Coupling that connects the motor shaft to the driven shaft.	C-302
4	Clean Dampers	Dedicated damper for suppressing stepping motor vibration.	C-310
(5)	Motor Lead Wire/Connector Assembly	Lead wire with a connector crimped for connector-coupled motors [0.6 m, 1 m (2 ft., 3.3 ft.)].	C-299
6	Driver Lead Wire Set	Cables for connecting the driver and motor, DC power supply or host controller [0.6 m (2 ft.)] (LCSO1CMK2).	C-301

●Example of System Configuration

(Sold separately)

CMK Series	+	Controller	Motor Mounting Bracket	Flexible Coupling	Clean Damper	Driver Lead Wire Set [0.6 m (2 ft.)]
CMK244PBP		SG8030J-U	PALOPA	MCS140506	D4CL-5.0F	LCS01CMK2

 $\ \, \blacksquare$ The system configuration shown above is an example. Other combinations are available.

■ Product Number Code

• High-Torque Type, High-Resolution Type, Standard Type

CMK 2 4 3 M A P A

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

SH Geared Type

CMK 2 6 4 A P A - SG 10

(1) (2) (3) (4) (5) (6) (7) (8)

Product Line

High-Torque Type

Model (Single shaft)	Model (Double shaft)
CMK223PAP	CMK223PBP
CMK224PAP	CMK224PBP
CMK225PAP	CMK225PBP
CMK233PAP	CMK233PBP
CMK235PAP	CMK235PBP
CMK244PAP	CMK244PBP
CMK246PAP	CMK246PBP

The following items are included in each product.

Motor, Driver, Driver Connector, Motor Lead Wire/Connector Assembly, Operating

High-Resolution Type

Model (Single shaft)	Model (Double shaft)
CMK243MAPA	CMK243MBPA
CMK244MAPA	CMK244MBPA
CMK245MAPA	CMK245MBPA
CMK264MAP	CMK264MBP
CMK266MAP	CMK266MBP
CMK268MAP	CMK268MBP

-The following items are included in each product. -Motor, Driver, Driver Connector, Operating Manual

Standard Type

Model (Double shaft)
СМК243ВРА
CMK244BPA
CMK245BPA
CMK256BP
CMK258BP
CMK264BP
CMK266BP
CMK268BP

The following items are included in each product. Motor, Driver, Driver Connector, Operating Manual

1	Series	CMK: CMK Series
2	2: 2-Phase	
3	Motor Frame Size	2 : 28 mm (1.10 in.) 3 : 35 mm (1.38 in.) 4 : 42 mm (1.65 in.) 5 : 50 mm (1.97 in.) 6 : 56.4 mm (2.22 in.)
4	Motor Case Length	
(5)	Motor Type	P : High-Torque Type Blank: Standard Type
6	Shaft Type	A: Single Shaft B: Double Shaft
7	Signal I/O Mode of Driver	P: Photocoupler
8	U.S.A. Version	

1	Series	CMK: CMK Series
2	2: 2-Phase	
3	Motor Frame Size	2 : 28 mm (1.10 in.) 4 : 42 mm (1.65 in.) 6 : 60 mm (2.36 in.)
4	Motor Case Length	
(5)	Shaft Type	A: Single Shaft B: Double Shaft
6	Signal I/O Mode of Driver	P: Photocoupler
7	U.S.A. Version	
8	Gearhead Type	SG: SH Geared Type
9	Gear Ratio	

SH Geared Type

Model (Single shaft)	Model (Double shaft)
CMK223AP-SG7.2	CMK223BP-SG7.2
CMK223AP-SG9	CMK223BP-SG9
CMK223AP-SG10	CMK223BP-SG10
CMK223AP-SG18	CMK223BP-SG18
CMK223AP-SG36	CMK223BP-SG36
CMK243APA-SG3.6	CMK243BPA-SG3.6
CMK243APA-SG7.2	CMK243BPA-SG7.2
CMK243APA-SG9	CMK243BPA-SG9
CMK243APA-SG10	CMK243BPA-SG10
CMK243APA-SG18	CMK243BPA-SG18
CMK243APA-SG36	CMK243BPA-SG36
CMK264APA-SG3.6	CMK264BPA-SG3.6
CMK264APA-SG7.2	CMK264BPA-SG7.2
CMK264APA-SG9	CMK264BPA-SG9
CMK264APA-SG10	CMK264BPA-SG10
CMK264APA-SG18	CMK264BPA-SG18
CMK264APA-SG36	CMK264BPA-SG36
	· ·

-The following items are included in each product. -

Motor, Driver, Driver Connector, Motor Lead Wire/Connector Assembly*, Mounting Screws for Motor, Operating Manual

*Only for connector-coupled motor

High-Torque Type Motor Frame Size 28 mm (1.10 in.)


■Specifications (RoHS)

Model	Single Shaft	CMK223PAP*	CMK224PAP*	CMK225PAP*		
Wodel	Double Shaft	CMK223PBP*	CMK224PBP*	CMK225PBP*		
Maximum Holding Torque	N·m (oz-in)	0.05 (7.1)	0.075 (10.6)	0.09 (12.7)		
Rotor Inertia J	kg·m² (oz-in²)	9×10 ⁻⁷ (0.049)	12×10 ⁻⁷ (0.066)	18×10 ⁻⁷ (0.098)		
Rated Current	A/Phase		0.95			
Basic Step Angle		1.8°				
Power Source		24 VDC±10% 1.5 A				
Excitation Mode		Microstep				
Mass	Motor kg (lb.)	0.11 (0.24)	0.14 (0.31)	0.2 (0.44)		
IVIGSS	Driver kg (lb.)	0.05 (0.11)				
Dimension No.	Motor		1			
יחווים ווחופווסוטוו ואט.	Driver		10			


How to read specifications table → Page C-11

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK223PAP/CMK223PBP



CMK224PAP/CMK224PBP



CMK225PAP/CMK225PBP



• The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%.

Notes:

- Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F).
- The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40%.

^{*}Motor lead wire/connector assembly [0.6 m (2 ft.)] is included with the connector-coupled motor and driver package.

High-Torque Type Motor Frame Size 35 mm (1.38 in.), 42 mm (1.65 in.)


■ Specifications (RoHS)

Model	Single Shaft	CMK233PAP*	CMK235PAP*	CMK244PAP*	CMK246PAP*		
Model	Double Shaft	CMK233PBP*	CMK235PBP*	CMK244PBP*	CMK246PBP*		
Maximum Holding Torque	N·m (oz-in)	0.16 (22)	0.3 (42)	0.39 (55)	0.75 (106)		
Rotor Inertia J	kg·m² (oz-in²)	24×10 ⁻⁷ (0.131)	50×10 ⁻⁷ (0.27)	57×10 ⁻⁷ (0.31)	114×10 ⁻⁷ (0.62)		
Rated Current	A/Phase		1.2				
Basic Step Angle		1.8°					
Power Source		24 VDC±10% 1.7 A					
Excitation Mode			Micro	ostep			
Mass	Motor kg (lb.)	0.18 (0.4)	0.285 (0.63)	0.3 (0.66)	0.5 (1.1)		
Mass	Driver kg (lb.)	0.05 (0.11)					
Dimension No.	Motor		2		3		
DITTETISION NO.	Driver		G	10			


How to read specifications table → Page C-11

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK233PAP/CMK233PBP




CMK235PAP/CMK235PBP



CMK244PAP/CMK244PBP



CMK246PAP/CMK246PBP



• The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%.

Notes

• Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F).

• The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40%.

^{*}Motor lead wire/connector assembly [0.6 m (2 ft.)] is included with the connector-coupled motor and driver package.

High-Resolution Type Motor Frame Size 42 mm (1.65 in.), 56.4 mm (2.22 in.)


■Specifications (RoHS)

Model	Single Shaft	CMK243MAPA	CMK244MAPA	CMK245MAPA	CMK264MAP	CMK266MAP	CMK268MAP
Model	Double Shaft	CMK243MBPA	CMK244MBPA	CMK245MBPA	CMK264MBP	CMK266MBP	CMK268MBP
Maximum Holding Torque	N·m (oz-in)	0.16 (22)	0.26 (36)	0.32 (45)	0.37 (52)	0.9 (127)	1.35 (191)
Rotor Inertia J	kg·m² (oz-in²)	35×10 ⁻⁷ (0.191)	54×10 ⁻⁷ (0.3)	68×10 ⁻⁷ (0.37)	120×10 ⁻⁷ (0.66)	300×10 ⁻⁷ (1.64)	480×10 ⁻⁷ (2.6)
Rated Current	A/Phase	0.95	1	.2		2	
Basic Step Angle				0.	9°		
Power Source		24 VDC±10% 1.5 A	24 VDC±1	10% 1.7 A		24 VDC±10% 2.9 A	
Excitation Mode				Micro	ostep		
Mass	Motor kg (lb.)	0.24 (0.53)	0.3 (0.66)	0.37 (0.81)	0.45 (0.99)	0.7 (1.54)	1 (2.2)
IVIdSS	Driver kg (lb.)		0.05 (0.11)				
Dimension No.	Motor		4			6	
	Driver		10				


How to read specifications table → Page C-11

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK243MAPA/CMK243MBPA




CMK244MAPA/CMK244MBPA




CMK245MAPA/CMK245MBPA




CMK264MAP/CMK264MBP



CMK266MAP/CMK266MBP



CMK268MAP/CMK268MBP



Notes

[•] The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%.

Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F).

The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40%.

Standard Type Motor Frame Size 42 mm (1.65 in.), 50 mm (1.97 in.)


■ Specifications (RoHS)

Model	Single S	haft	CMK243APA	CMK244APA	CMK245APA	CMK256AP	CMK258AP	
Wodei	Double S	Shaft	CMK243BPA	CMK244BPA	CMK245BPA	CMK256BP	CMK258BP	
Maximum Holding Torque	N	l·m (oz-in)	0.16 (22)	0.26 (36)	0.32 (45)	0.56 (79)	1.2 (170)	
Rotor Inertia J	kg∙r	m² (oz-in²)	35×10 ⁻⁷ (0.191)	54×10 ⁻⁷ (0.3)	68×10 ⁻⁷ (0.37)	230×10 ⁻⁷ (1.26)	420×10 ⁻⁷ (2.3)	
Rated Current		A/Phase	0.95	0.95				
Basic Step Angle					1.8°			
Power Source			24 VDC±10% 1.5 A	24 VDC±	10% 1.7 A	24 VDC±10% 2.9 A		
Excitation Mode					Microstep			
Mana	Motor	kg (lb.)	0.21 (0.46)	0.27 (0.59)	0.35 (0.77)	0.53 (1.17)	0.89 (1.96)	
Mass	Driver	kg (lb.)	0.05 (0.11)					
Dimension No -	Motor			4		[5	
	Driver				10			

How to read specifications table → Page C-11

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK243APA/CMK243BPA



CMK245APA/CMK245BPA



CMK258AP/CMK258BP




■ The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%.

Notes:


• Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F).

 $\bullet \text{ The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40\%. }$

CMK244APA/CMK244BPA



CMK256AP/CMK256BP



Standard Type Motor Frame Size 56.4 mm (2.22 in.)


■ Specifications (RoHS)

Model	Single Shaft	CMK264AP	CMK266AP	CMK268AP			
Wodel	Double Shaft	CMK264BP	CMK266BP	CMK268BP			
Maximum Holding Torque	N·m (oz-in)	0.36 (51)	0.36 (51) 0.82 (116)				
Rotor Inertia J	kg·m² (oz-in²)	120×10 ⁻⁷ (0.66)	300×10 ⁻⁷ (1.64)	480×10 ⁻⁷ (2.6)			
Rated Current	A/Phase		2				
Basic Step Angle			1.8°				
Power Source			24 VDC±10% 2.9 A				
Excitation Mode			Microstep				
Mass	Motor kg (lb.)	0.45 (0.99)	0.7 (1.54)	1 (2.2)			
IVIASS	Driver kg (lb.)	0.05 (0.11)					
Dimension No.	Motor		6				
טוווופוופוטוו ואט.	Driver		10	·			


How to read specifications table → Page C-11

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK264AP/CMK264BP



CMK266AP/CMK266BP



CMK268AP/CMK268BP



• The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%.

Notes

Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F).
 The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40%.

SH Geared Type Motor Frame Size 28 mm (1.10 in.)

■ Specifications (RoHS)

Model	Single Shaft	CMK223AP-SG7.2*	CMK223AP-SG9*	CMK223AP-SG10*	CMK223AP-SG18*	CMK223AP-SG36*	
Model	Double Shaft	CMK223BP-SG7.2*	CMK223BP-SG9*	CMK223BP-SG10*	CMK223BP-SG18*	CMK223BP-SG36*	
Maximum Holding Torque	N·m (oz-in)		0.3 (42)		0.4 (56)		
Rotor Inertia J	kg·m² (oz-in²)			9×10 ⁻⁷ (0.049)			
Rated Current	A/Phase			0.95			
Basic Step Angle		0.25°	0.2°	0.18°	0.1°	0.05°	
Gear Ratio		7.2:1	9:1	10:1	18:1	36:1	
Permissible Torque	N·m (oz-in)		0.3 (42)		0.4 (56)		
Permissible Speed Range	r/min	0~250	0~200	0~180	0~100	0~50	
Power Source				24 VDC±10% 1.5 A			
Excitation Mode				Microstep			
Mooo	Motor kg (lb.)			0.16 (0.35)			
Mass	Driver kg (lb.)	0.05 (0.11)					
Dimension No.	Motor			7			
	Driver			10			

How to read specifications table → Page C-11


*Motor lead wire/connector assembly [0.6 m (2 ft.)] is included with the connector-coupled motor and driver package.

Notes:


- Backlash value is approximately 1 to 2°.
- Direction of rotation of the motor and that of the gear output shaft are the same for gear ratios 7.2:1 and 36:1. It is the opposite for 9:1, 10:1 and 18:1 gear ratios.

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK223AP-SG7.2/CMK223BP-SG7.2




CMK223AP-SG10/CMK223BP-SG10




CMK223AP-SG36/CMK223BP-SG36



CMK223AP-SG9/CMK223BP-SG9



CMK223AP-SG18/CMK223BP-SG18



 \bullet The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%.

Notes

- Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F)
- The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40%.

SH Geared Type Motor Frame Size 42 mm (1.65 in.)

■Specifications (RoHS)

Model	Single Shaft	CMK243APA-SG3.6	CMK243APA-SG7.2	CMK243APA-SG9	CMK243APA-SG10	CMK243APA-SG18	CMK243APA-SG36	
Model	Double Shaft	CMK243BPA-SG3.6	CMK243BPA-SG7.2	CMK243BPA-SG9	CMK243BPA-SG10	CMK243BPA-SG18	CMK243BPA-SG36	
Maximum Holding Torque	N•m (lb-in)	0.2 (1.77)	0.4 (3.5)	0.5 (4.4)	0.56 (4.9)	0.8 (7)		
Rotor Inertia J	kg·m² (oz-in²)			35×10	⁷ (0.191)			
Rated Current	A/Phase			0.	95			
Basic Step Angle		0.5°	0.25°	0.2°	0.18°	0.1°	0.05°	
Gear Ratio		3.6:1	7.2:1	9:1	10:1	18:1	36:1	
Permissible Torque	N·m (lb-in)	0.2 (1.77)	0.4 (3.5)	0.5 (4.4)	0.56 (4.9)	0.8	(7)	
Permissible Speed Range	r/min	0~500	0~250	0~200	0~180	0~100	0~50	
Power Source				24 VDC±	10% 1.5 A			
Excitation Mode				Micr	ostep			
Mass	Motor kg (lb.)			0.35	(0.77)			
IvidSS	Driver kg (lb.)		0.05 (0.11)					
Dimonoion No	Motor			[8			
Dimension No.	Driver			[10			

How to read specifications table → Page C-11


Notes:

Backlash value is approximately 1 to 2°.


Direction of rotation of the motor and that of the gear output shaft are the same for gear ratios 3.6:1, 7.2:1, 9:1 and 10:1. It is the opposite for 18:1 and 36:1 gear ratios

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK243APA-SG3.6/ CMK243BPA-SG3.6




CMK243APA-SG7.2/ CMK243BPA-SG7.2




CMK243APA-SG9/ CMK243BPA-SG9




CMK243APA-SG10/ CMK243BPA-SG10



CMK243APA-SG18/ CMK243BPA-SG18



CMK243APA-SG36/ CMK243BPA-SG36



 \blacksquare The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%

Notes

- Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F).
- The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40%.

SH Geared Type Motor Frame Size 60 mm (2.36 in.)

Specifications (RoHS)

Model	Single Shaft	CMK264APA-SG3.6	CMK264APA-SG7.2	CMK264APA-SG9	CMK264APA-SG10	CMK264APA-SG18	CMK264APA-SG36	
Wiodei	Double Shaft	CMK264BPA-SG3.6	CMK264BPA-SG7.2	CMK264BPA-SG9	CMK264BPA-SG10	CMK264BPA-SG18	CMK264BPA-SG36	
Maximum Holding Torque	N•m (lb-in)	1 (8.8)	2 (17.7)	2.5 (22)	2.7 (23)	3 (26)	4 (35)	
Rotor Inertia J	kg·m² (oz-in²)			120×1	0-7 (0.66)			
Rated Current	A/Phase				2			
Basic Step Angle		0.5°	0.25°	0.2°	0.18°	0.1°	0.05°	
Gear Ratio		3.6:1	7.2:1	9:1	10:1	18:1	36:1	
Permissible Torque	N•m (lb-in)	1 (8.8)	2 (17.7)	2.5 (22)	2.7 (23)	3 (26)	4 (35)	
Permissible Speed Range	r/min	0~500	0~250	0~200	0~180	0~100	0~50	
Power Source				24 VDC±	10% 2.9 A			
Excitation Mode				Micr	ostep			
Mooo	Motor kg (lb.)			0.75	(1.65)			
Mass	Driver kg (lb.)		0.05 (0.11)					
Dimension No.	Motor			[9			
	Driver				10			


How to read specifications table → Page C-11

Notes:


- Backlash value is approximately 1 to 2°.
- Direction of rotation of the motor and that of the gear output shaft are the same for gear ratios 3.6:1, 7.2:1, 9:1 and 10:1. It is the opposite for 18:1 and 36:1 gear ratios.

Speed - Torque Characteristics How to read speed - torque characteristics → Page C-12


CMK264APA-SG3.6/ CMK264BPA-SG3.6




CMK264APA-SG7.2/ CMK264BPA-SG7.2




CMK264APA-SG9/ CMK264BPA-SG9




CMK264APA-SG10/ CMK264BPA-SG10



CMK264APA-SG18/ CMK264BPA-SG18



CMK264APA-SG36/ CMK264BPA-SG36



• The pulse input circuit responds to approximately 100 kHz with a pulse duty of 50%.

Notes:

- Pay attention to heat dissipation from motor as there will be a considerable amount of heat under certain conditions. Be sure to keep the temperature of the motor case under 100°C (212°F).
- The driver's automatic current cutback function at motor standstill reduces maximum holding torque by approximately 40%.

Driver Specifications

	Input Mode	Photocoupler input Pulse (CW pulse) signal, Rotation direction (CCW pulse) signal: Input resistance $200~\Omega$, Input current $5\sim20~\text{mA}$ Photocoupler ON: $+3\sim5.25~\text{V}$, Photocoupler OFF: $0\sim+1~\text{V}$ (Voltage between terminals) All windings off signal, Step angle select signal, Automatic current cutback release signal: Input resistance $3.3~\text{k}\Omega$, Input current $1~\text{mA}~(5~\text{VD}C)/8~\text{mA}~(24~\text{VDC})$ Photocoupler ON: $+4.5\sim26.4~\text{V}$, Photocoupler OFF: $0\sim+1~\text{V}$ (Voltage between terminals)
	Pulse Signal (CW Pulse Signal)	Operation command pulse signal (CW direction operation command pulse signal when in 2-pulse input mode), Negative logic pulse input Pulse width: 5 µs minimum, Pulse rise/fall: 2 µs maximum, Pulse duty: 50% and below Motor moves one step when the pulse input is switched from ON to OFF. Maximum input pulse frequency: 100 kHz (When the pulse duty is 50%)
Input Signals	Rotation Direction Signal (CCW Pulse Signal)	Rotation direction signal, Photocoupler ON: CW, Photocoupler OFF: CCW CCW direction operation command pulse signal when in 2-pulse input mode, Negative logic pulse input Pulse width: 5 µs minimum, Pulse rise/fall: 2 µs maximum, Pulse duty: 50% and below Motor moves one step when the pulse input is switched from photocoupler ON to OFF Maximum input pulse frequency: 100 kHz (When the pulse duty is 50%)
	All Windings Off Signal	When in the "photocoupler ON" state, the output current to the motor is cut off and the motor shaft can be rotated manually. When in the "photocoupler OFF" state, the current is supplied to the motor.
	Step Angle Select Signal	When in the "photocoupler ON" state, the motor operates at the basic step angle regardless of the settings of the step angle setting switches. When in the "photocoupler OFF" state, the motor operates at the step angle set by the step angle setting switches.
	Automatic Current Cutback Release Signal	When in the "photocoupler ON" state, the automatic current cutback function will not be activated even after the motor stops. When in the "photocoupler OFF" state, the automatic current cutback function will be activated after the motor stops (after approx. 100 msec).
	Output Mode	Photocoupler, Open-collector output External use condition: 24 VDC maximum, 10 mA maximum
Output Signal	Excitation Timing Signal	The signal is output every time the excitation sequence returns to the initial stage "0." (Photocoupler: ON) •High-torque type, standard type 1.8°/step [Microsteps/step: 1 (Resolution: 200)]: Signal is output every 4 pulses 0.45°/step [Microsteps/step: 4 (Resolution: 800)]: Signal is output every 16 pulses •High-resolution type 0.9°/step [Microsteps/step: 1 (Resolution: 400)]: Signal is output every 4 pulses 0.225°/step [Microsteps/step: 4 (Resolution: 1600)]: Signal is output every 16 pulses •SH geared type (gear ratio 18:1) 0.1°/step [Microsteps/step: 1 (Resolution: 3600)]: Signal is output every 4 pulses 0.025°/step [Microsteps/step: 4 (Resolution: 14400)]: Signal is output every 16 pulses
Functions		Automatic current cutback, Step angle select, Pulse input mode switch, All windings off, Excitation timing
Cooling Metho	od	Natural ventilation


■General Specifications

Ite	em	Motor	Driver		
Insulation Class		Class B [130°C (266°F)]	_		
Insulation Resistance		$100~\mbox{M}\Omega$ or more when 500 VDC megger is applied between the windings and the case under normal ambient temperature and humidity.	-		
Dielectric Strength		Sufficient to withstand 1.0 kVAC at 50 Hz or 60 Hz applied between the windings and the case for 1 minute under normal ambient temperature and humidity. [0.5 kVAC for models with frame size 42 mm (1.65 in.) or smaller]	_		
	Ambient Temperature	$-10\sim+50^{\circ}\text{C}$ (+14 $\sim+122^{\circ}\text{F}$) (non-freezing)	$0\sim+40^{\circ}\text{C} \ (+32\sim+104^{\circ}\text{F}) \ (\text{non-freezing})$		
Operating Environment	Ambient Humidity	85% or less (no	on-condensing)		
	Atmosphere	No corrosive gases, dust, water or oil			
Temperature Rise		Temperature rise of windings is 80°C (144°F) or less measured by the resistance change method. (at rated voltage, at standstill, two phases energized)	_		
Stop Position Accuracy*1		±3 arc minutes (±0.05°)	-		
Shaft Runout		0.05 mm (0.002 in.) T.I.R.*4	-		
Radial Play*2		0.025 mm (0.001 in.) maximum of 5 N (1.12 lb.)	_		
Axial Play*3		0.075 mm (0.003 in.) maximum of 10 N (2.2 lb.)	-		
Concentricity		0.075 mm (0.003 in.) T.I.R.*4	_		
Perpendicularity	<u> </u>	0.075 mm (0.003 in.) T.I.R.*4	_		

- $\ensuremath{ \star 1}$ This value is for full step under no load. (The value changes with the size of the load.)
- *2 Radial Play: Displacement in shaft position in the radial direction, when a 5 N (1.12 lb.) load is applied in the vertical direction to the tip of the motor's shaft.
- *3 Axial Play: Displacement in shaft position in the axial direction, when a 10 N (2.2 lb.) load is applied to the motor's shaft in the axial direction.
- *4 T.I.R. (Total Indicator Reading): The total dial gauge reading when the measurement section is rotated one revolution centered on the reference axis center.

Note:

lacktriangle Do not measure insulation resistance or perform the dielectric strength test while the motor and driver are connected.



				Derminsible			
Type	Model			Distance from Shaft End	ı		Permissible Thrust Load
		0 mm (0 in.)	5 mm (0.2 in.)	10 mm (0.39 in.)	15 mm (0.59 in.)	20 mm (0.79 in.)	IIIIust Lodu
	CMK223P□P CMK224P□P CMK225P□P	25 (5.6)	34 (7.6)	52 (11.7)	-	_	
High-Torque Type	CMK233P□P CMK235P□P	20 (4.5)	25 (5.6)	34 (7.6)	52 (11.7)	_	
	CMK244P□P CMK246P□P	20 (4.5)	25 (5.6)	34 (7.6)	52 (11.7)	_	
High David High Tops	CMK243M□PA CMK244M□PA CMK245M□PA	20 (4.5)	25 (5.6)	34 (7.6)	52 (11.7)	_	The permissible
High-Resolution Type	CMK264M□P CMK266M□P CMK268M□P	54 (12.1)	67 (15)	89 (20)	130 (29)	-	thrust load shall be no greater than the motor mass.
	CMK243□PA CMK244□PA CMK245□PA	20 (4.5)	25 (5.6)	34 (7.6)	52 (11.7)	_	
Standard Type	CMK256□P CMK258□P	54 (12.1)	67 (15)	89 (20)	130 (29)	_	
	CMK264□P CMK266□P CMK268□P	54 (12.1)	67 (15)	89 (20)	130 (29)	-	
	CMK223 P-SG7.2 CMK223 P-SG9 CMK223 P-SG10 CMK223 P-SG18 CMK223 P-SG36	15 (3.3)	17 (3.8)	20 (4.5)	23 (5.1)	_	10 (2.2)
SH Geared Type	CMK243 PA-SG3.6 CMK243 PA-SG7.2 CMK243 PA-SG9 CMK243 PA-SG10 CMK243 PA-SG18 CMK243 PA-SG36	10 (2.2)	15 (3.3)	20 (4.5)	30 (6.7)	-	15 (3.3)
	CMK264□PA-SG3.6 CMK264□PA-SG7.2 CMK264□PA-SG9 CMK264□PA-SG10	30 (6.7)	40 (9)	50 (11.2)	60 (13.5)	70 (15.7)	30 (6.7)
	CMK264□PA-SG18 CMK264□PA-SG36	80 (18)	100 (22)	120 (27)	140 (31)	160 (36)	

lacktriangle Enter **A** (single shaft) or **B** (double shaft) in the box (\Box) within the model name.

28 (**1.10**)

23±0.2 (0.906±0.008)

16.5 (0.65)

35 (1.38)

(1.142±0.008)

23 (0.91)

4×M3×4.5 (0.18) Deep

±0.008) 29±0.2 1.142±0.7 35 (1.3

Dimensions Unit = mm (in.)

Motor

♦ High-Torque Type

1 □ 28 mm (□1.10 in.)

Model	Motor Model	L1	L2	Mass kg (lb.)	DXF
CMK223PAP	PK223PA	32	_	0.11	B326
CMK223PBP	PK223PB	(1.26)	42 (1.65)	(0.24)	D320
CMK224PAP	PK224PA	40	_	0.14	B327
CMK224PBP	PK224PB	(1.57)	50 (1.97)	(0.31)	DSZI
CMK225PAP	PK225PA	51.5	_	0.2	B328
CMK225PBP	PK225PB	(2.03)	61.5 (2.42)	(0.44)	D320


Motor lead wire/connector assembly of 0.6 m (2 ft.) is included with the package. UL Style

If you are purchasing only a motor for maintenance purpose, etc., motor lead wire/connector assembly and connector will not be supplied. They must be purchased separately.

→ Page C-299

Applicable Connector

Connector housing: 51065-0600 (MOLEX) Contact: 50212-8100 (MOLEX) Crimp tool: 57176-5000 (MOLEX)



*The length of machining on the double shaft model is 10±0.25 (0.394±0.010)

2 □35 mm (□1.38 in.)

Model	Motor Model	L1	L2	Mass kg (lb.)	DXF
CMK233PAP	PK233PA	37	_	0.18	B329
CMK233PBP	PK233PB	(1.46)	52 (2.05)	(0.4)	DSZ9
CMK235PAP	PK235PA	52	_	0.285	B330
CMK235PBP	PK235PB	(2.05)	67 (2.64)	(0.63)	D330


Motor lead wire/connector assembly of 0.6 m (2 ft.) is included with the package. UL Style 3265. AWG24

If you are purchasing only a motor for maintenance purpose, etc., motor lead wire/connector assembly and connector will not be supplied. They must be purchased separately.

→ Page C-299

Applicable Connector

Connector housing: 51103-0600 (MOLEX) Contact: 50351-8100 (MOLEX) Crimp tool: 57295-5000 (MOLEX)



*The length of machining on the double shaft model is 15±0.25 (0.591±0.010).

These dimensions are for the double shaft models. For the single shaft models, ignore the orange () areas.

3 □42 mm (□1.65 in.)


Model	Motor Model	L1	L2	Mass kg (lb.)	DXF
CMK244PAP	PK244PA	39	_	0.3	B331
CMK244PBP	PK244PB	(1.54)	54 (2.13)	(0.66)	DOOT
CMK246PAP	PK246PA	59	_	0.5	B332
CMK246PBP	PK246PB	(2.32)	74 (2.91)	(1.1)	DOOZ

Motor lead wire/connector assembly of 0.6 m (2 ft.) is included with the package. UL Style 3265, AWG24 $\,$

If you are purchasing only a motor for maintenance purpose, etc., motor lead wire/connector assembly and connector will not be supplied. They must be purchased separately.

- → Page C-299
- Applicable Connector

Connector housing: 51103-0600 (MOLEX) Contact: 50351-8100 (MOLEX) Crimp tool: 57295-5000 (MOLEX)




*The length of machining on the double shaft model is 15±0.25 (0.591±0.010).

♦ High-Resolution Type, Standard Type

4 □42 mm (□1.65 in.)

Model	Motor Model	L1	L2	Mass kg (lb.)	DXF	
CMK243APA	PK243-01AA			0.21 (0.46)		
CMK243MAPA	PK243MAA	33	_	0.24 (0.53)	B081U	
CMK243BPA	PK243-01BA	(1.3)	48	0.21 (0.46)	DUOTU	
CMK243MBPA	PK243MBA		(1.89)	0.24 (0.53)		
CMK244APA	PK244-01AA			0.27 (0.59)		
CMK244MAPA	PK244MAA	39	_	0.3 (0.66)	B082U	
CMK244BPA	PK244-01BA	(1.54)	54	0.27 (0.59)		
CMK244MBPA	PK244MBA	(2.13)		0.3 (0.66)		
CMK245APA	PK245-01AA			0.35 (0.77)		
CMK245MAPA	PK245MAA	47	_	0.37 (0.81)	B083U	
CMK245BPA	PK245-01BA	(1.85)	62	0.35 (0.77)	DU03U	
CMK245MBPA	PK245MBA		(2.44)	0.37 (0.81)		



*The length of machining on the double shaft model is 15±0.25 (0.591±0.010).


[•] These dimensions are for the double shaft models. For the single shaft models, ignore the orange () areas.

With Encode

\diamondsuit Standard Type

5 □50 mm (□1.97 in.)

Model	Motor Model	L1	L2	Mass kg (lb.)	DXF
CMK256AP	PK256-02A	51.5	_	0.53	B333
CMK256BP	PK256-02B	(2.03)	67.5 (2.66)	(1.17)	DOOO
CMK258AP	PK258-02A	81	_	0.89	B334
CMK258BP	PK258-02B	(3.19)	97 (3.82)	(1.96)	D334







♦ High-Resolution Type, Standard Type

6 □56.4 mm (□2.22 in.)

Model	Motor Model	L1	L2	Mass kg (lb.)	DXF
CMK264AP	PK264-02A				
CMK264MAP	PK264MA	39	_	0.45	B084
CMK264BP	PK264-02B	(1.54)	55	(0.99)	DU04
CMK264MBP	PK264MB		(2.17)		
CMK266AP	PK266-02A				
CMK266MAP	PK266MA	54	_	0.7	B085
CMK266BP	PK266-02B	(2.13)	70	(1.54)	
CMK266MBP	PK266MB		(2.76)		
CMK268AP	PK268-02A				
CMK268MAP	PK268MA	76	_	1.0	B086
CMK268BP	PK268-02B	(2.99)	92	(2.2)	DUOO
CMK268MBP	PK268MB		(3.62)		





These dimensions are for the double shaft models. For the single shaft models, ignore the orange (_____) areas.

♦ SH Geared Type

7 □28 mm (□1.10 in.)

Model	Motor Model	Gear Ratio	Mass kg (lb.)	DXF
CMK223AP-SG□	PK223PA-SG□	7. 2, 9, 10, 18, 36	0.16	B335
CMK223BP-SG□	PK223PB-SG□	7.2, 9, 10, 18, 30	(0.35)	

• Enter the gear ratio in the box (□) within the model name.

Motor lead wire/connector assembly of 0.6 m (2 ft.) is included with the package. UL Style 3265. AWG24


If you are purchasing only a motor for maintenance purpose, etc., motor lead wire/connector assembly and connector will not be supplied. They must be purchased separately.

- → Page C-299
- Screws (Included)

M2.5 Length 8 mm (0.31 in.) --- 4 pieces

Applicable Connector

Connector housing: 51065-0600 (MOLEX) Contact: 50212-8100 (MOLEX) Crimp tool: 57176-5000 (MOLEX)



*The length of machining on the double shaft model is 10 ± 0.25 (0.394 ±0.010).


8 □42 mm (□1.65 in.)

Model	Motor Model	Gear Ratio	Mass kg (lb.)	DXF
CMK243APA-SG□	PK243A1A-SG□	3.6 , 7.2 , 9 , 10 ,	0.35	B091U
CMK243BPA-SG	PK243B1A-SG□	18, 36	(0.77)	50910

 \bullet Enter the gear ratio in the box (\square) within the model name.

Screws (Included)

No.4-40 UNC Length 10 mm (0.39 in.) ··· 4 pieces



[•] These dimensions are for the double shaft models. For the single shaft models, ignore the orange (_____) areas.

9 □60 mm (□2.36 in.)

Model	Motor Model	Gear Ratio	Mass kg (lb.)	DXF	[]/16	
CMK264APA-SG	PK264A2A-SG□	3.6 , 7.2 , 9 , 10 ,	0.75	B092U		
CMK264BPA-SG	PK264B2A-SG□	18, 36	(1.65)	D0920	0.0006	
Enter the gear ratio in t	the box (\square) within th	ne model name.			25-[
Screws (Included) No.8-32 UNC Length 1	5.8 mm (0.62 in.) ···	4 pieces	\$\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	(900	7.5±01 (0.29g	(2.76±0.02) (2.76±0.02) (2.76±0.02) (2.86) (2.76±0.02) (2.86) (2.76±0.02) (2.76±0.02)

6 Motor Leads 300 mm (12 in.) Length

UL Style 3265, AWG22


• These dimensions are for the double shaft models. For the single shaft models, ignore the orange () areas.

Driver

10CMD2109P, CMD2112P, CMD2120P

Mass: 0.05 kg (0.11 lb.)

DXF B441



Connector Housing (Included)

51103-0200 (MOLEX)

51103-1200 (MOLEX)

51103-0600 (MOLEX)

Contact (Included)50351-8100 (MOLEX)


Note:

• Use the included connector for power supply, signal and motor. When assembling the connectors, use the hand-operated crimp tool [57295-5000 (MOLEX)]. The crimp tool is not included with the package. It must be purchased separately.

Driver lead wire set crimped with connector is available (sold separately). → Page C-301

■Connection and Operation

Names and Functions of Driver Parts



1 Power Input Display

Color Function		When Activated		
Green	Power supply indication	Lights when power is on.		

2 Current Adjustment Switches

Indication	Switch Name	Function	
RUN	Motor run current switch	For adjusting the motor running current.	
ST0P	Motor stop current potentiometer	For adjusting the motor current at standstill.	

3 Function Select Switches

Indicati	n Switch Name	Function
1	Pulse input mode switch	Switches between 1-pulse input and 2-pulse input.
2, 3,	Step angle setting switch	These switches can be set to the desired resolution from the five resolution levels.

Step Angle Setting Switches

SW-2	SW-3	SW-4	Microsteps/Step	Resolution	Step Angle
0FF	0FF	0FF	1	200	1.8°
0FF	0FF	ON	2	400	0.9°
0FF	ON	0FF	4	800	0.45°
0FF	ON	ON	8	1600	0.225°
ON	0FF	0FF	16	3200	0.1125°

Notes


- Use of any setting other than the combinations listed in the table will automatically set the microstep to "1" and the motor will operate at the basic step angle.
- The step angle is calculated by dividing the basic step angle by the number of microsteps. The above figures are based on a basic step angle of 1.8°.
- With the high-resolution type, the basic step angle and resolution are 0.9° and 400 (microsteps/step 1) respectively.
- If you are using a geared type, the step angle divided by the gear ratio becomes the actual step angle.
- The step angle set with the step angle setting switches will become effective when the "Step Angle Select" (CS) signal input is OFF.
- Do not change the "Step Angle Select" (CS) signal input or step angle setting switches while the motor is operating. It may cause the motor to misstep and stop. Change the step angle setting switches, when the "Step Angle Select" (CS) signal input is OFF and the "Excitation Timing" (TIM) signal output is ON.

4 Input/Output Signals

Indication	Input/ Output	Pin No.	Signal Name	Function		
		1	Pulse signal	Operation command pulse signal (The motor will rotate in the CW direction		
		2	(CW pulse signal)	when in 2-pulse input mode.)		
		3	Rotation direction	Rotation direction signal Photocoupler ON: CW, Photocoupler OFF: CCW		
		4	(CCW pulse signal)	(The motor will rotate in the CCW direction when in 2-pulse input mode.)		
	Input	5	All windings off signal Step angle select signal Automatic current cutback release signal	Cuts the output current to the motor and allows the motor shafts to be rotated		
CN2	iliput	6		manually.		
OIVE		7		The motor will operate at the basic step angle regardless of the settings of the ste		
		8		angle setting switches.		
		9		This signal is used to disable the automatic		
		10		current cutback function.		
	Output	11	Excitation timing	Outputs signals when the excitation		
	Output	12	signal	sequence is at STEP "0."		

Description of input/output signals → Page C-201

Connection Diagram



Pulse (CW) Signal, Rotation Direction (CCW) Signal

Signals can be connected directly when 5 VDC is supplied. If the signals are used at a voltage exceeding 5 VDC, be sure to provide an external resistor to prevent the current exceeding 20 mA from flowing. Internal components will be damaged if a voltage exceeding 5 VDC is supplied directly without using an external resistor.

Example: If the voltage is 24 VDC, connect a resistor (R₁) of 1.5 to 2.2 k Ω and 0.5 W or more.

 All Windings Off Signal, Step Angle Select Signal, Automatic Current Cutback Release Signal

Signals can be connected directly when 5 to 24 VDC is supplied.

○Output Signal Connection

Use the output signal at 24 VDC or less and 10 mA or less. If these specifications are exceeded, the internal components may get damaged. Check the specification of the connected equipment. When the current is above 10 mA, connect an external resistor B₂.

◇Power Supply

Use a power supply that can supply sufficient input current. When power supply capacity is insufficient, a decrease in motor output can cause the following malfunctions:

- Motor does not rotate properly at high-speed
- Slow motor startup and stopping

♦ Notes on Wiring

- Use twisted-pair wires of AWG24~22 and keep wiring as short as possible [within 2 m (6.6 ft.)].
- Note that as the length of the pulse signal line increases, the maximum transmission frequency decreases. Technical reference → Page F-54
- Use wires of AWG22 or thicker for power supply lines. When assembling the connector, use the hand-operated crimp tool or the crimped driver lead wire set (sold separately). The crimp tool is not provided with the package. It must be purchased separately.
- Provide a minimum distance of 2 cm (0.79 in.) between the signal lines and power lines (AC lines, motor lines and other large-current circuits).
 Do not run the signal lines in the same duct as power lines or bundle them with power lines.
- If noise generated by the motor lead wires causes a problem, insert ferrite cores in the motor lead wire.
- Incorrect connection of DC power input will lead to driver damage. Make sure that the polarity is correct before turning power on.


Description of Input/Output Signals

Indication of Input/Output Signal "ON""OFF"


Input (output) "ON" indicates that the current is sent into the photocoupler (transistor) inside the driver. Input (output) "OFF" indicates that the current is not sent into the photocoupler (transistor) inside the driver. The input/output remains "OFF" if nothing is connected.

Pulse (CW) and Rotation Direction (CCW) Input Signal


♦ Input Circuit and Sample Connection



• 1-Pulse Input Mode



• 2-Pulse Input Mode




Pulse duty: 50% and below

- *1 The shaded area indicates that the photocoupler diode is ON. The motor moves when the photocoupler state changes from ON to OFF.
- *2 The minimum interval time when changing rotation direction is 10 μs. This value varies greatly depending on the motor type and load inertia.

- Keep the pulse signal at the "photocoupler OFF" state when no pulses are being input.
- In 1-pulse input mode, leave the pulse signal at rest ("photocoupler OFF") when changing rotation directions.
- In 2-pulse input mode, do not input a CW pulse and CCW pulse simultaneously.


All Windings Off (AWO) Input Signal Step Angle Select (CS) Input Signal Automatic Current Cutback Release (ACDOFF) Input Signal

♦ Input Circuit and Sample Connection



♦ All Windings Off (AWO) Input Signal

- Inputting this signal puts the motor in a non-excitation (free) state.
- This signal is used when moving the motor by external force or manual home position is desired. The photocoupler must be "OFF" when operating the motor.



The shaded area indicates that the motor provides holding torque in proportion to standstill current set by STOP switch.

 Switching the "All Windings Off" (AWO) signal from "photocoupler ON" to "photocoupler OFF" does not alter the excitation sequence.

When the motor shaft is manually adjusted with the "All Windings Off" signal input, the shaft will shift up to $\pm 3.6^\circ$ (geared type: $\pm 3.6^\circ$ /gear ratio) from the position set after the "All Windings Off" signal is released.


♦ Step Angle Select (CS) Input Signal

- When this signal input is "ON," the motor will operate at the basic step angle regardless of the settings of the step angle setting switches. When the signal input is "OFF," the motor will operate at the step angle set with the step angle setting switches.
- To change the step angle, do so when the "Excitation Timing" signal output is "ON" and the motor is at standstill.

- When this signal is in the "photocoupler ON" state, the automatic current cutback function is disabled. When this signal is in the "photocoupler OFF" state, the automatic current cutback function will be activated after the motor stops (after approx. 100 msec).
- The photocoupler must be "OFF" when the motor is operating.

Excitation Timing (TIM) Output Signal

♦ Output Circuit and Sample Connection




- The "Excitation Timing" signal is output to indicate when the motor excitation is in the initial stage (step "0" at power up).
- The "Excitation Timing" signal is output simultaneously with a pulse input each time the excitation sequence returns to step "0." The excitation sequence will complete one cycle for every 7.2° (3.6° for high-resolution type) rotation of the motor output shaft.

Microsteps/step 1: Signal is output once every 4 pulses. Microsteps/step 4: Signal is output once every 16 pulses.


Timing chart at 1.8°/step (Microsteps/step 1)

* When connected as shown in the sample connection, the signal will be "photocoupler ON" at step "0."



Notes:

- When power is turned ON, the excitation sequence is reset to step "0" and the "Excitation Timing" signal is output.
- When operating the motor using the "Excitation Timing" signal output, make sure the motor output shaft stops at an integral multiple of 7.2° (3.6° for high-resolution type).



The section indicates that the photocoupler diode is emitting light.

- *1 The minimum switching time to change direction (1-pulse input mode), and switching time to change CW, CCW pulse (2-pulse input mode) 10 µs is shown as a response time of circuit. The motor may need more time than that.
- *2 Depends on load inertia, load torque and starting frequency.
- *3 Never input a pulse signal immediately after switching the "All Windings Off" signal to "photocoupler OFF." The motor may not start.
- *4 Wait at least 5 seconds before turning on the power again.

List of Motor and Driver Combinations

Model names for motor and driver combinations are shown below.

Type	Model	Motor Model	Driver Model
1360	CMK223PAP	PK223PA*	Silvoi modoi
	CMK223PBP	PK223PB*	
	CMK224PAP	PK224PA*	
	CMK224PBP	PK224PB*	CMD2109P
	CMK225PAP	PK225PA*	
	CMK225PBP	PK225PB*	
	CMK233PAP	PK233PA*	
High-Torque Type	CMK233PBP	PK233PB*	
	CMK235PAP	PK235PA*	
	CMK235PBP	PK235PB*	CUD0110D
	CMK244PAP	PK244PA*	CMD2112P
	CMK244PBP	PK244PB*	
	CMK246PAP	PK246PA*	
	CMK246PBP	PK246PB*	
	CMK243MAPA	PK243MAA	CHECTOOL
	CMK243MBPA	PK243MBA	CMD2109P
	CMK244MAPA	PK244MAA	
	CMK244MBPA	PK244MBA	CMD0110D
	CMK245MAPA	PK245MAA	CMD2112P
High-Resolution Type	CMK245MBPA	PK245MBA	
nigii-nesolullori Type	CMK264MAP	PK264MA	
	CMK264MBP	PK264MB	
	CMK266MAP	PK266MA	CMD2120P
	CMK266MBP	PK266MB	CMD21201
	CMK268MAP	PK268MA	
	CMK268MBP	PK268MB	
	CMK243APA	PK243-01AA	CMD2109P
	CMK243BPA	PK243-01BA	CMDZ109F
	CMK244APA	PK244-01AA	
	CMK244BPA	PK244-01BA	CMD2112P
	CMK245APA	PK245-01AA	CIVIDZTTZI
	CMK245BPA	PK245-01BA	
	CMK256AP	PK256-02A	
Standard Type	CMK256BP	PK256-02B	
January 13po	CMK258AP	PK258-02A	
	CMK258BP	PK258-02B	
	CMK264AP	PK264-02A	CMD2120P
	CMK264BP	PK264-02B	CITIDETECT
	CMK266AP	PK266-02A	
	CMK266BP	PK266-02B	
	CMK268AP	PK268-02A	
	CMK268BP	PK268-02B	

Type	Model	Motor Model	Driver Model
SH Geared Type	Model CMK223AP-SG7.2 CMK223BP-SG9 CMK223BP-SG9 CMK223AP-SG10 CMK223BP-SG10 CMK223BP-SG18 CMK223BP-SG18 CMK223BP-SG36 CMK223BP-SG36	Motor Model PK223PA-SG7.2* PK223PB-SG7.2* PK223PA-SG9* PK223PA-SG10* PK223PA-SG10* PK223PA-SG18* PK223PA-SG18* PK223PA-SG36* PK223PB-SG36*	Driver Model
	CMK243APA-SG3.6 CMK243APA-SG3.6 CMK243APA-SG7.2 CMK243BPA-SG7.2 CMK243APA-SG9 CMK243APA-SG10 CMK243APA-SG10 CMK243APA-SG18 CMK243APA-SG18 CMK243APA-SG36 CMK243APA-SG36	PK243A1A-SG3.6 PK243B1A-SG3.6 PK243B1A-SG7.2 PK243B1A-SG7.2 PK243B1A-SG9 PK243B1A-SG9 PK243B1A-SG10 PK243B1A-SG10 PK243B1A-SG18 PK243B1A-SG36 PK243B1A-SG36	CMD2109P
	CMK264APA-SG3.6 CMK264BPA-SG3.6 CMK264APA-SG7.2 CMK264BPA-SG7.2 CMK264APA-SG9 CMK264APA-SG10 CMK264APA-SG10 CMK264APA-SG18 CMK264BPA-SG18 CMK264APA-SG36 CMK264APA-SG36	PK264A2A-SG3.6 PK264B2A-SG3.6 PK264B2A-SG7.2 PK264B2A-SG7.2 PK264B2A-SG9 PK264B2A-SG9 PK264B2A-SG10 PK264B2A-SG10 PK264B2A-SG18 PK264B2A-SG18 PK264B2A-SG36 PK264B2A-SG36	CMD2120P

If you are purchasing only a motor for maintenance purpose, etc., motor lead wire/connector assembly will not be supplied. They must be purchased separately.

Motor lead wire/connector assembly → Page C-299

EMP400

SG8030J

They are available as accessories.